

PHILIPS

Steam iron

EasySpeed Advanced

2400 W


180 g steam boost

40 g/min continuous steam

Ceramic soleplate



GC2676/29



Faster from start to finish

Speeds up your ironing in 5 ways

Make ironing faster from start to finish with Easyspeed Advanced steam iron: quick heat-up, XL water hole, powerful bursts of steam to tackle tough creases, durable ceramic soleplate for quick gliding and our drip-stop system. Five ways to speed up your ironing!

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Up to 180 g steam boost blasts stubborn creases
- Steam output up to 40 g/min for strong, steady performance
- Extra-large water hole for fast filling and emptying
- Triple precision tip for optimal control and visibility

Easy ironing

- Automatic shut-off when iron is left unattended
- Durable ceramic soleplate for easy gliding
- Drip-stop system keeps garments spotless while ironing
- Extra-long 2.5 metre cord for easy reach
- Easy cord wrapping with clip for quick, tidy storage

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

Highlights

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

Steam boost up to 180 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 40 g/min of steam




Strong and consistent steam output to remove creases faster.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

Automatic shut-off



The iron shuts itself off if you leave it standing still. On its heel rest, it will automatically switch off in 8 minutes. Lying flat, it shuts down after 30 motionless seconds.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

Extra-long 2.5 m cord



An extra-long 2.5 metre cord provides maximum reach to anywhere on the ironing board and convenience.

Cord wrapping with clip



The cord is easily wrapped around the base of the iron and held in place with a clip for tidy storage.

Specifications

Fast crease removal

Continuous steam: 40 g/min
Power: 2400 W
Steam boost: 180 g
Variable steam levels
Vertical steam
Water spray

Easy to use

Soleplate name: Ceramic
Water tank capacity: 300 ml
Cord freedom (swivel): 360 degree cord freedom

Power cord length: 2.5 m
Precision steam tip
Tap water suitable
Drip-stop
Extra-large filling hole
Auto shut-off

Scale management

Descaling and cleaning: Self-clean

Storage

Cord storage: Cord clip

Size and weight

Weight of iron: 1.150 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
User manual: 100% recycled paper

Technical specifications

Heating time: 30 sec.

