



Steam iron

- 2400 W
- 180 g steam boost
- 40 g/min continuous steam
- Ceramic soleplate

GC2676/29

Faster from start to finish

Speeds up your ironing in 5 ways

Make ironing faster from start to finish with Easyspeed Advanced steam iron: quick heat-up, XL water hole, powerful bursts of steam to tackle tough creases, durable ceramic soleplate for quick gliding and our drip-stop system. Five ways to speed up your ironing!

Benefits

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Up to 180 g steam boost blasts stubborn creases
- Steam output up to 40 g/min for strong, steady performance
- Extra-large water hole for fast filling and emptying
- Triple precision tip for optimal control and visibility

Easy ironing

- Automatic shut-off when iron is left unattended

- Durable ceramic soleplate for easy gliding
- Drip-stop system keeps garments spotless while ironing
- Extra-long 2.5 metre cord for easy reach
- Easy cord wrapping with clip for quick, tidy storage

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

PHILIPS

Features

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

Steam boost up to 180 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 40 g/min of steam



Strong and consistent steam output to remove creases faster.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

Automatic shut-off



The iron shuts itself off if you leave it standing still. On its heel rest, it will automatically switch off in 8 minutes. Lying flat, it shuts down after 30 motionless seconds.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

Extra-long 2.5 m cord



An extra-long 2.5 metre cord provides maximum reach to anywhere on the ironing board and convenience.

Cord wrapping with clip



The cord is easily wrapped around the base of the iron and held in place with a clip for tidy storage.

EasySpeed Advanced

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Continuous steam	40 g/min
Power	2400 W
Steam boost	180 g
Variable steam levels	Yes
Vertical steam	Yes
Water spray	Yes

Easy to use

Soleplate name	Ceramic
Water tank capacity	300 ml
Cord freedom (swivel)	360 degree cord freedom
Power cord length	2.5 m
Precision steam tip	Yes
Tap water suitable	Yes
Drip-stop	Yes
Extra-large filling hole	Yes
Auto shut-off	Yes

Scale management

Descaling and cleaning	Self-clean
------------------------	------------

Storage

Cord storage	Cord clip
--------------	-----------

Size and weight

Weight of iron	1.150 kg
----------------	----------

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

Energy saving mode	Yes
User manual	100% recycled paper

Technical specifications

Heating time	30 sec.
--------------	---------

Packaging dimensions

Height	16.00 cm
Width	31.50 cm
Depth	14.00 cm
Net weight	1.24 kg
Gross weight	1.48 kg
EAN	08710103851417
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851640

Outer Carton

Length	43.00 cm
Width	32.50 cm
Height	34.00 cm
Gross weight	9.43 kg
EAN	18710103851414
Number of consumer packages	6



data subject to change
2018, October 18

Version: 6.0.1
EAN: 08710103851417

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com