

# PHILIPS

## Steam iron

### EasySpeed Advanced

2400 W

190 g steam boost

40 g/min continuous steam

Ceramic soleplate



GC2678/39



## Faster from start to finish

### Speeds up your ironing in 5 ways

Make ironing faster from start to finish: quick heat-up, XL water hole, powerful bursts of steam to tackle tough creases, durable ceramic soleplate for quick gliding and our drip-stop system. That's five ways to speed up your ironing.

#### Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Up to 190 g steam boost blasts stubborn creases
- Steam output up to 40 g/min for strong, steady performance
- Extra-large water hole for fast filling and emptying
- Triple precision tip for optimal control and visibility

#### Easy ironing

- Automatic shut-off when iron is left unattended
- Durable ceramic soleplate for easy gliding
- Drip-stop system keeps garments spotless while ironing
- Extra-long 2.5 metre cord for easy reach
- Easy cord wrapping with clip for quick, tidy storage

#### Long-lasting performance

- Calc-clean slider for long-lasting steam performance

# Highlights

## 2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

## Steam boost up to 190 g



Penetrates deeper into fabrics to easily remove stubborn creases.

## Up to 40 g/min of steam




Strong and consistent steam output to remove creases faster.

## XL water filling hole




An extra-large opening for filling the water tank makes quick work of refills and emptying.

## Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

## Automatic shut-off



The iron shuts itself off if you leave it standing still. On its heel rest, it will automatically switch off in 8 minutes. Lying flat, it shuts down after 30 motionless seconds.

## Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

## Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

## Extra-long 2.5 m cord



An extra-long 2.5 metre cord provides maximum reach to anywhere on the ironing board and convenience.

## Cord wrapping with clip



The cord is easily wrapped around the base of the iron and held in place with a clip for tidy storage.

# Specifications

## Fast crease removal

Continuous steam: 40 g/min  
Power: 2400 W  
Steam boost: 190 g  
Variable steam levels  
Vertical steam  
Water spray

## Easy to use

Soleplate name: Ceramic  
Water tank capacity: 300 ml  
Cord freedom (swivel): 360 degree cord freedom

Power cord length: 2.5 m  
Precision steam tip  
Tap water suitable  
Drip-stop  
Extra-large filling hole  
Auto shut-off

## Scale management

Descaling and cleaning: Self-clean

## Storage

Cord storage: Cord clip

## Size and weight

Weight of iron: 1.150 kg

## Guarantee

2 year worldwide guarantee

## Green efficiency

Energy saving mode  
User manual: 100% recycled paper

## Technical specifications

Heating time: 30 sec.

