

PHILIPS

Steam iron

PowerLife

2000W

30 g/min steam



GC2910/27



Built to perform, day after day

Iron with SteamGlide soleplate

For great results day after day, you want an iron that never lets you down. With its new SteamGlide soleplate, for constant high steam output and easy to use calc clean this practical Philips steam iron gives you value for money that lasts!

Easily removes creases

- Steam boost up to 90 g for the most stubborn creases
- Continuous steam up to 30 g/min for better crease removal

Powerful performance

- 2000 Watt enables constant high steam output

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Longer lifetime

- Calc clean slider to easily remove scale out of your iron

Protects your garments

- Drip-stop system keeps your garments spotless while ironing

Highlights

2000 Watt

2000 W
max

2000 Watt enables constant high steam output.

Up to 30 g/min of steam



Continuous steam up to 30 g/min for better crease removal.

Steam boost up to 90 g



The iron's 90 g steam boost enables you to easily remove even the most stubborn creases.

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.

Calc clean slider



This steam iron can be operated with normal tap water and the calc clean slider makes it easy to remove any built-up scale out of your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Drip-stop system



The Drip Stop system of your Philips steam iron lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide
Variable steam settings
Spray

Easy to use

Water tank capacity: 300 ml
Drip stop
Cord freedom (swivel): 360 degree cord freedom
Power cord length: 2 m

Calc management

Suitable for tap water
Calc clean solution: Self clean

Technical specifications

Power Global: 2000 W
Voltage: 220-240 V

Weight and dimensions

Product dimensions: 29.5 x 11.6 x 19.5
Product weight: 1.2 kg

Crease removal

Continuous steam: Up to 30 gr/min
Steam Boost: Up to 90 gr/min

