

# PHILIPS

## Steam iron

### PowerLife

Steam 35g/min; 110g steam boost

SteamGlide soleplate

Anti-calc

2200 Watts



GC2920/70



## Built to perform, day after day

### Iron with SteamGlide soleplate

For great results day after day, you want an iron that never lets you down. With its new SteamGlide soleplate, for constant high steam output and Calc buster pill, this practical Philips steam iron gives you value for money that lasts!

#### **Easily removes creases**

- Continuous steam output up to 35 g/min
- 110-g steam boost to remove stubborn creases easily
- Vertical steam for crease removal in hanging fabrics

#### **Powerful performance**

- Powerful steam for fast ironing

#### **Easy gliding on all fabrics**

- SteamGlide soleplate is Philips premium soleplate

#### **Longer lifetime**

- Calc clean slider to easily remove scale out of your iron
- The calc pill breaks down calc so you can flush away easily

# Highlights

## 2200 Watt

**2200 W**  
**max**

This powerful iron heats up quickly and maintains very stable temperatures during ironing, making it easier to remove creases properly.

## Steam output up to 35 g/min



Continuous steam output of up to 35 g/min gives you the perfect amount of steam to efficiently remove all creases.

## Steam boost up to 110 g



The iron's 110 g steam boost enables you to easily remove even the most stubborn creases.

## SteamGlide soleplate



The SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistance, glides excellently and is easy to clean.

## Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your


iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

## Calc buster pill

**Calc  
buster  
pill**

After time calc builds up in your iron. This tablet breaks the calc down in to pieces so you can calc clean your iron easily. This cleaning needs to happen once a month.

## Vertical steam



**Vertical  
shot of steam**

This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

# Specifications

## Fast and powerful crease removal

Soleplate: SteamGlide  
Vertical steaming  
Variable steam settings  
Spray

## Comfortable ironing

Cord length: 1.8 m

## Easy to use

Water tank capacity: 300 ml  
Drip stop  
Cord freedom (swivel): 360 degree cord

freedom

Power cord length: 1.8 m outside Europe, 1.9 m within Europe

## Calc management

Suitable for tap water  
Calc clean solution: Double active calc clean

## Technical specifications

Power Global: 2200 W  
Power China: 1850 W  
Voltage: 220-240 V

## Weight and dimensions

Product dimensions: 29.5 x 11.6 x 19.5  
Product weight: 1.2 kg

## Crease removal

Continuous steam: Up to 35 gr/min  
Steam Boost: Up to 110 gr/min

