

PHILIPS

Steam iron

PowerLife

Steam 35g/min; 120g steam boost

SteamGlide soleplate

Anti-calc

2300 Watts



GC2930/30



Built to perform, day after day

With SteamGlide soleplate

For great results day after day, you want an iron that never lets you down. With its new SteamGlide soleplate, constant high steam output and Calc buster pill, this practical iron gives you value for money that lasts!

Powerful performance

- Powerful steam for fast ironing

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Easily removes creases

- Continuous steam output up to 35 g/min
- 120 g steam boost to remove stubborn creases easily
- Vertical steam for crease removal in hanging fabrics

Longer lifetime

- The calc pill breaks down calc so you can flush away easily
- Calc clean slider to easily remove scale out of your iron

Highlights

2300 Watt

2300 W
max

This powerful iron heats up quickly and maintains very stable temperatures during ironing, making it easier to remove creases properly.

Steam output up to 35 g/min




Continuous steam output of up to 35 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 120 g



The iron's 120 g steam boost enables you to easily remove even the most stubborn creases.

Vertical steam



This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

SteamGlide soleplate



The SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistance, glides excellently and is easy to clean.

Calc buster pill

**Calc
buster
pill**

After time calc builds up in your iron. This tablet breaks the calc down in to pieces so you can calc clean your iron easily. This cleaning needs to happen once a month.

Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide
Vertical steaming
Variable steam settings
Spray
Continuous steam output: 35 g/min
Power: 2300 W
Steam boost: 120 g

Comfortable ironing

Cord length: 1.8 m

Easy to use

Water tank capacity: 300 ml
Drip stop
Cord freedom (swivel): 360 degree cord freedom
Extra stability: Rubber bumper
Power cord length: 1.8 m

Calc management

Suitable for tap water
Calc clean solution: Double active calc clean

Technical specifications

Product dimensions: 29.5 x 11.6 x 19.5 cm
Product weight: 1.2 kg
Voltage: 220-240 V

