

PHILIPS

Steam iron

PowerLife

2200 W

35 g/min steam

110 g steam boost



GC2965/27



Built for powerful ironing

Iron with electronic safety shut-off

For great results day after day, you want an iron that never lets you down. With its new SteamGlide soleplate, constant high steam output and Calc buster pill, this practical Philips Steam iron gives you value for money that lasts!

Easily removes creases

- Continuous steam output up to 35 g/min
- 110 g steam boost to remove stubborn creases easily

Powerful performance

- Powerful steam for fast ironing

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Comfortable ironing

- Vertical steam for crease removal in hanging fabrics
- Cord freedom with the 360 degree swivel solution

Safe ironing

- 3 ways of automatic shut-off



Highlights

2200 Watt

2200 W
max

This powerful iron heats up quickly and maintains very stable temperatures during ironing, making it easier to remove creases properly.

Steam output up to 35 g/min




Continuous steam output of up to 35 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 110 g



The iron's 110 g steam boost enables you to easily remove even the most stubborn creases.

Vertical steam



Vertical shot of steam

This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.

Cord freedom

Cord freedom with the 360 degree swivel solution

Automatic shut-off

Safety auto off

Iron shuts off automatically when the iron is hold still for 30s on soleplate, 30s lying on a side or standing on its heel rest for 8 minutes.

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide
Vertical steaming
Variable steam settings
Spray

Easy to use

Water tank capacity: 300 ml
Drip stop
Safety auto off
Cord freedom (swivel): 360 degree cord freedom
Extra stability: Rubber bumper
Power cord length: 2 m

Calc management

Suitable for tap water
Calc clean solution: Double active calc clean

Technical specifications

Power Global: 2200 W
Voltage: 220-240 V

Weight and dimensions

Product dimensions: 29.5 x 11.6 x 19.5
Product weight: 1.2 kg

Crease removal

Continuous steam: Up to 35 gr/min
Steam Boost: Up to 110 gr/min

