

PHILIPS

Steam iron

PowerLife

Steam 40g/min; 130g steam boost

SteamGlide soleplate

Anti-calc

2400 Watts



GC2965/35



Built to perform, day after day

Iron with heat-resistant storage box

For great results day after day, you want an iron that never lets you down. With its SteamGlide soleplate, constant high steam output and Calc buster pill, this Philips iron gives you value for money that lasts! Now with a storage box.

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Longer lifetime

- Calc clean slider to easily remove scale out of your iron
- The calc pill breaks down calc so you can flush away easily

Easily removes creases

- Continuous steam output up to 40 g/min
- 130 g steam boost to remove stubborn creases easily
- 2400 W for quick heat up
- Vertical steam for crease removal in hanging fabrics

Easy storage

- Heat-resistant storage box for easy storage

Highlights

SteamGlide soleplate



The SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistance, glides excellently and is easy to clean.

Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Calc buster pill

Calc buster pill

After time calc builds up in your iron. This tablet breaks the calc down in to pieces so you can calc clean your iron easily. This cleaning needs to happen once a month.

Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 130 g




The steam boost can be used for vertical steaming and tough creases.

2400 W for quick heat up

2400 W max

2400 W for quick heat-up and powerful performance


Vertical steam



Vertical shot of steam

This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

Heat-resistant storage box



This heat-resistant storage box is designed for storing the hot iron easily. For optimal performance and longer lifetime of your box, always unplug the iron and empty the water tank before storing the iron in the box. When you put a hot iron in the box, the bottom of the box also becomes warm on the outside, but there is no risk of burning.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide
Steam output: Up to 40 gr/min
Steam boost: 130 g
Vertical steaming

Comfortable ironing

Cord length: 1.8 m

Easy to use

Water tank capacity: 300 ml
Drip stop
Extra stability: Rubber bumper

Calc management

Calc clean solution: Double active calc clean

Technical specifications

Power Global: 2400 W

Accessories

Heat-resistant storage box

Crease removal

Reaching tricky areas: Pointed tip

Extra convenience

Pointed tip

