

PHILIPS

Steam iron

PowerLife Plus

Steam 40g/min; 150g steam boost

SteamGlide soleplate

Anti-calc

2400 Watts

GC2988/80



Built to perform, day after day

The Philips PowerLife Plus steam iron gives great results day after day and never lets you down, with its new SteamGlide soleplate, constant high-steam output, easy to use calc clean for long-lasting steam and an extra-stable heel rest.

Fast and powerful performance

- 2400 W for quick heat up
- Steam output of up to 40 g/min for better crease removal
- 150 g steam boost to remove stubborn creases easily

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Safe ironing

- Calc clean slider to easily remove scale out of your iron
- Robust heel rest for improved stability
- Drip-stop system keeps your garments spotless while ironing
- Iron switches off automatically when left unattended

Highlights

2400 W for quick heat up



2400 W for quick heat-up and powerful performance

Steam up to 40 g/min



Continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 150 g



The iron's 150 g steam boost enables you to easily remove even the most stubborn creases.

SteamGlide soleplate



The SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistance, glides excellently and is easy to clean.

Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Drip-stop system



Your Philips steam iron's Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Robust heel rest

This iron features a specially designed extra-large heel rest, which gives extra stability when it is put in a vertical position.

Safety auto off



The iron shuts off automatically when left unattended. If it is left on its heelrest it will switch off in 8 minutes. When left on the soleplate or on the side, it only takes 30 seconds before the iron shuts off.

Specifications

Easy to use

Drip stop
Power cord length: 2 m
Water tank capacity: 300 ml
Safety auto off

Fast and powerful crease removal

Continuous steam output: 40 g/min
Power: 2400 W
Soleplate: SteamGlide
Steam boost: 150 g

Green efficiency

Energy saving*: 20 %

Scale management

Descaling and cleaning: Built-in calc container

Fast crease removal

Vertical steam
Water spray

