

PHILIPS

Steam iron

PowerLife

2300 W

40 g/min continuous steam

140 g steam boost

SteamGlide soleplate



GC2990/26



Built to perform, day after day

4x longer life with SteamGlide soleplate*

For great results day after day, you want an iron that never lets you down. With its anti-scratch SteamGlide soleplate, high consistent steam output and integrated calc-clean, this high quality iron gives you performance that lasts.

Fast & powerful crease removal

- 2300 W to heat up quickly
- Up to 140 g steam boost blasts stubborn creases
- Steam output up to 40 g/min for strong, steady performance
- Vertical steaming for hanging fabrics

Long lasting performance

- Built-in calc-clean slider, long-lasting steam performance
- Tested cord for maximum durability and safety
- Scratch resistant SteamGlide soleplate provides good gliding

Comfortable ironing

- Comfortable, textured handle for easy grip
- Drip-stop keeps garments spotless while ironing



asimpleswitch.com

Highlights

2300 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Steam boost up to 140 g




Penetrates deeper into fabrics to easily remove stubborn creases.

Continuous steam up to 40g/min



Strong and consistent steam output to remove creases faster.

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

SteamGlide soleplate



Our special SteamGlide soleplate smoothly glides over any fabric. It's also non-stick, scratch-resistant and easy to clean.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium buildup, or limescale, and maintain peak performance.

Quality-tested cord



All our steam iron cords are rigorously tested for maximum safety and durability.

No more messy dripping



Our Drip Stop system lets you iron delicate fabrics at low temperatures with confidence. There's no need to worry about water droplets causing stains.

Comfortable handle



A textured handle ensures you a comfortable, ergonomic grip, so you can keep hold of the iron without ever slipping.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast crease removal

Water spray
Continuous steam: 40 g/min
Power: 2300 W
Steam boost: 140 g

Easy to use

Water tank capacity: 320 ml
Drip Stop
Extra stable heel rest

Tap water suitable
Extra large filling hole
Soleplate name: SteamGlide

Scale management

Descaling and cleaning: Built-in Calc Clean
Slider

Size and weight

Packaging dimensions (WxHxL):
33.2x16.7x13.7 cm
Product dimensions (WxHxL):
31.2x14.7x12.7 cm
Weight of iron: 1.255 kg

Guarantee

2 year worldwide guarantee

Green efficiency

User manual: 100% recycled paper

