



Steam iron

- 2400 W
- 40 g/min continuous steam
- 150 g steam boost
- SteamGlide soleplate

GC2994/26

Built to perform, day after day

4 x longer life with SteamGlide soleplate*

For great results day after day, you want an iron that never lets you down. With its anti-scratch SteamGlide soleplate, consistent high steam output and integrated calc-clean, this high-quality iron gives you performance that lasts.

Benefits

Fast and powerful crease removal

- 2400 W to heat up quickly
- Up to 150 g steam boost blasts stubborn creases
- Steam output up to 40 g/min for strong, steady performance
- Vertical steaming for hanging fabrics

Long-lasting performance

- SteamGlide soleplate — superior gliding and scratch resistance

- Built-in calc-clean slider, long-lasting steam performance
- 2.5m cord tested for maximum durability and safety

Comfortable ironing

- Drip stop keeps garments spotless while ironing
- Comfortable, textured handle for easy grip

PHILIPS

Features

2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Steam boost up to 150 g

Penetrates deeper into fabrics to easily remove stubborn creases.

Continuous steam up to 40 g/min



Strong and consistent steam output to remove creases faster

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

SteamGlide soleplate

Our exclusive SteamGlide soleplate moves smoothly over any fabric. A durable, 5 layer coating—including anti-corrosive base—makes it last longer. Non-stick, scratch-resistant and easy to keep clean.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Quality-tested cord



All our steam iron cables are rigorously tested for maximum safety and durability.

No more messy dripping



Our Drip Stop system lets you iron delicate fabrics at low temperatures with confidence. There's no need to worry about water droplets causing stains.

Comfortable handle



A textured handle ensures you a comfortable, ergonomic grip, so you can keep hold of the iron without ever slipping.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Water spray	Yes
Continuous steam	40 g/min
Power	2400 W
Steam boost	150 g

Easy to use

Water tank capacity	320 ml
Drip Stop	Yes
Extra-stable heel rest	Yes
Tap water suitable	Yes
Extra-large filling hole	Yes
Soleplate name	SteamGlide

PowerLife

Scale management

Descaling and cleaning	Built-in Calc-Clean Slider
------------------------	----------------------------

Size and weight

Packaging dimensions (W x H x D)	33.2 x 16.7 x 13.7 cm
Product dimensions (W x H x D)	31.2 x 14.7 x 12.7 cm
Weight of iron	1.255 kg

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

User manual	100% recycled paper
-------------	---------------------

Packaging dimensions

Height	16.70 cm
--------	----------

Width	33.20 cm
Depth	13.70 cm
Net weight	1.28 kg
Gross weight	1.49 kg
EAN	08710103812739
Number of products included	1
Country of origin	ID
Harmonised Systems Code	851640

Outer Carton

Length	34.40 cm
Width	42.10 cm
Height	34.60 cm
Gross weight	9.50 kg
EAN	18710103812736
Number of consumer packages	6

* **Tested vs. Philips non-stick soleplate



data subject to change
2017, November 9

Version: 9.0.1
EAN: 08710103812739

© 2017 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com