

PHILIPS

Steam iron

PowerLife

2400 W

40 g/min continuous steam

150 g steam boost

SteamGlide soleplate



GC2994/29



Built to perform, day after day

4 x longer life with SteamGlide soleplate*

For great results day after day, you want an iron that never lets you down. With its anti-scratch SteamGlide soleplate, consistent high steam output and integrated calc-clean, this high-quality iron gives you performance that lasts.

Comfortable ironing

- Comfortable, textured handle for easy grip
- Drip stop keeps garments spotless while ironing

Fast and powerful crease removal

- 2400 W to heat up quickly
- Steam output up to 40 g/min for strong, steady performance
- Up to 150 g steam boost blasts stubborn creases
- Vertical steaming for hanging fabrics

Long-lasting performance

- Built-in calc-clean slider, long-lasting steam performance
- Tested cord for maximum durability and safety
- SteamGlide soleplate — superior gliding and scratch resistance

Highlights

2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Continuous steam up to 40 g/min




Strong and consistent steam output to remove creases faster

Steam boost up to 150 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

SteamGlide soleplate



Our exclusive SteamGlide soleplate moves smoothly over any fabric. A durable, 5 layer coating—including anti-corrosive base—makes it last longer. Non-stick, scratch-resistant and easy to keep clean.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Quality-tested cord



All our steam iron cables are rigorously tested for maximum safety and durability.

No more messy dripping



Our Drip Stop system lets you iron delicate fabrics at low temperatures with confidence. There's no need to worry about water droplets causing stains.

Comfortable handle



A textured handle ensures you a comfortable, ergonomic grip, so you can keep hold of the iron without ever slipping.

Specifications

Fast crease removal

Continuous steam: 40 g/min
Power: 2400 W
Steam boost: 150 g
Water spray

Easy to use

Soleplate name: SteamGlide
Water tank capacity: 320 ml
Drip Stop
Extra-stable heel rest
Tap water suitable
Extra-large filling hole

Comfortable ironing

Cord length: 2.5 m

Scale management

Descaling and cleaning: Built-in Calc-Clean Slider

Accessories included

CordGuide

Size and weight

Packaging dimensions (W x H x D): 33.2 x 16.7 x 13.7 cm
Product dimensions (W x H x D): 31.2 x 14.7 x 12.7 cm
Weight of iron: 1.255 kg

Guarantee

2 year worldwide guarantee

Green efficiency

User manual: 100% recycled paper

