



Steam iron

- 2400 W
- 40 g/min continuous steam
- 150 g steam boost
- SteamGlide soleplate

GC2994/29

Built to perform, day after day

4 x longer life with SteamGlide soleplate*

For great results day after day, you want an iron that never lets you down. With its anti-scratch SteamGlide soleplate, consistent high steam output and integrated calc-clean, this high-quality iron gives you performance that lasts.

Benefits

Comfortable ironing

- Drip stop keeps garments spotless while ironing
- Comfortable, textured handle for easy grip

Fast and powerful crease removal

- 2400 W to heat up quickly
- Steam output up to 40 g/min for strong, steady performance
- Up to 150 g steam boost blasts stubborn creases

- Vertical steaming for hanging fabrics

Long-lasting performance

- SteamGlide soleplate — superior gliding and scratch resistance
- Built-in calc-clean slider, long-lasting steam performance
- Tested cord for maximum durability and safety

PHILIPS

Features

2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Continuous steam up to 40 g/min



Strong and consistent steam output to remove creases faster

Steam boost up to 150 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

SteamGlide soleplate



Our exclusive SteamGlide soleplate moves smoothly over any fabric. A durable, 5 layer coating—including anti-corrosive base—makes it last longer. Non-stick, scratch-resistant and easy to keep clean.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Quality-tested cord



All our steam iron cables are rigorously tested for maximum safety and durability.

No more messy dripping



Our Drip Stop system lets you iron delicate fabrics at low temperatures with confidence. There's no need to worry about water droplets causing stains.

Comfortable handle



A textured handle ensures you a comfortable, ergonomic grip, so you can keep hold of the iron without ever slipping.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

| | |
|------------------|----------|
| Continuous steam | 40 g/min |
| Power | 2400 W |
| Steam boost | 150 g |
| Water spray | Yes |

Easy to use

| | |
|---------------------|------------|
| Soleplate name | SteamGlide |
| Water tank capacity | 320 ml |

PowerLife

| | |
|--------------------------|-----|
| Drip Stop | Yes |
| Extra-stable heel rest | Yes |
| Tap water suitable | Yes |
| Extra-large filling hole | Yes |

Comfortable ironing

| | |
|-------------|-------|
| Cord length | 2.5 m |
|-------------|-------|

Scale management

| | |
|------------------------|----------------------------|
| Descaling and cleaning | Built-in Calc-Clean Slider |
|------------------------|----------------------------|

Accessories included

| | |
|-----------|-----|
| CordGuide | Yes |
|-----------|-----|

Size and weight

| | |
|----------------------------------|-----------------------|
| Packaging dimensions (W x H x D) | 33.2 x 16.7 x 13.7 cm |
| Product dimensions (W x H x D) | 31.2 x 14.7 x 12.7 cm |
| Weight of iron | 1.255 kg |

Guarantee

| | |
|----------------------------|-----|
| 2 year worldwide guarantee | Yes |
|----------------------------|-----|

Green efficiency

| | |
|-------------|---------------------|
| User manual | 100% recycled paper |
|-------------|---------------------|

Packaging dimensions

| | |
|-----------------------------|----------------|
| Height | 16.70 cm |
| Width | 33.20 cm |
| Depth | 13.70 cm |
| Net weight | 1.28 kg |
| Gross weight | 1.49 kg |
| EAN | 08710103815891 |
| Number of products included | 1 |
| Country of origin | ID |
| Harmonised Systems Code | 851640 |

Outer Carton

| | |
|-----------------------------|----------------|
| Length | 34.40 cm |
| Width | 42.10 cm |
| Height | 34.60 cm |
| Gross weight | 9.50 kg |
| EAN | 18710103815898 |
| Number of consumer packages | 6 |

* Tested vs. Philips non-stick soleplate



data subject to change
2018, June 16

Version: 1.0.1
EAN: 08710103815891

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com