

PHILIPS

Steam iron

PowerLife

2400 W

45 g/min continuous steam

160 g steam boost

SteamGlide soleplate



GC2995/37



Built to perform, day after day

4 x longer life with SteamGlide soleplate*

With its anti-scratch SteamGlide soleplate, consistent high steam output and anti calc technology, thePowerlife steam iron gives you performance that lasts.

Fast and powerful crease removal

- 2400 W to heat up quickly
- Up to 160 g steam boost blasts stubborn creases
- Steam output up to 45 g/min for strong, steady performance
- Vertical steaming for hanging fabrics

Long-lasting performance

- Scratch-resistant SteamGlide soleplate provides good gliding
- Built-in calc-clean slider, long-lasting steam performance
- 2.5m cord tested for maximum durability and safety

Comfortable ironing

- Drip stop keeps garments spotless while ironing
- Comfortable, textured handle for easy grip
- Heat resistant box for immediate storage after ironing



asimpleswitch.com

Highlights

2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Steam boost up to 160 g




Penetrates deeper into fabrics to easily remove stubborn creases.

Continuous steam up to 45 g/min



Strong and consistent steam output to remove creases faster.

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

SteamGlide soleplate



Our special SteamGlide soleplate smoothly glides over any fabric. It's also non stick, scratch resistant and easy to clean.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Quality-tested cord



All our steam iron cables are rigorously tested for maximum safety and durability.

No more messy dripping



Our Drip Stop system lets you iron delicate fabrics at low temperatures with confidence. There's no need to worry about water droplets causing stains.

Comfortable handle



A textured handle ensures you a comfortable, ergonomic grip, so you can keep hold of the iron without ever slipping.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast crease removal

Water spray
Continuous steam: 45 g/min
Power: 2400 W
Steam boost: 160 g

Easy to use

Water tank capacity: 320 ml
Drip Stop
Extra-stable heel rest

Tap water suitable
Extra-large filling hole
Soleplate name: SteamGlide

Scale management

Descaling and cleaning: Built-in Calc-Clean
Slider

Storage

Storage solution: Heat resistant box

Size and weight

Packaging dimensions (W x H x D): 33.2 x 16.7
x 13.7 cm
Product dimensions (W x H x D): 31.2 x 14.7 x
12.7 cm
Weight of iron: 1.255 kg

Guarantee

2 year worldwide guarantee

Green efficiency

User manual: 100% recycled paper

