

PHILIPS

Steam iron

GC3220



Great results, minimum effort

3x easier

EasyCare - Makes the art of looking smart easier!

Easily removes creases

- Extra-large water inlet for fast, easy filling
- Extra-long cord for maximum reach
- Extra-clear indicator for highly visible water level

Reaches into tricky areas

- The pointed tip makes ironing along buttons and seams easy

Comfortable ironing

- Less refilling with extra-large 300 ml water tank

Easy crease removal from cotton and linen

- SteamGlide soleplate is Philips premium soleplate

Highlights

Extra-large water inlet



With the extra-large water inlet, adding water to your iron is quick and easy. It only takes a few seconds, and there's no more risk of spilling water everywhere!

Extra-long cord length




With EasyCare's extra-long 3 m cord, you can easily reach right up to the edges of your ironing board – and further!

Highly visible water level



The extra-clear indicator of your Philips iron, makes the water level highly visible, so you always know if you have enough water at a glance.

Pointed tip



The pointed tip makes ironing along buttons and seams easy.

Specifications

Comfortable ironing

Additional comfort: 360 degree cord freedom,
Extra-clear water level indicator
Cord length: 3 m
Water tank capacity: 300 ml

Crease removal

Continuous steam: Up to 35 gr/min
Reaching tricky areas: Pointed tip
Spray
Steam Boost: Up to 90 gr/min
Vertical Steam

Easy to use

Easy to set up and store: Extra-large water inlet, Integrated cord storage solution
Fast heat-up

Smooth gliding

Soleplate: SteamGlide soleplate

Technical specifications

Frequency: 50-60
Power: 2200
Voltage: 220 - 240

Weight and dimensions

Product dimensions: 303 x 120 x 152
Product weight: 1,34

