

PHILIPS

Steam iron

3300 series

3m cord

GC3320



Great results, minimum effort

3x easier

This Philips steam iron offers you not only extra convenience because of the large water inlet, extra-long cord and water-level indicator; its new SteamGlide soleplate also makes ironing easier and smoother!

Reaches into tricky areas

- Pointed tip for ironing tricky areas

Comfortable ironing

- Drip-stop system keeps your garments spotless while ironing
- Extra-large water inlet for fast, easy filling
- Extra-long cord for maximum reach
- Extra-clear indicator for highly visible water level

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Highlights

Extra-large water inlet



With the extra-large water inlet, adding water to your iron is quick and easy. It only takes a few seconds, and there's no more risk of spilling water everywhere!

Extra-long cord

With the extra-long cord, you can easily reach right up to the edges of your ironing board - and further!

Highly visible water level



The extra-clear indicator makes the water level highly visible, so you always know if you have enough water at a glance.

Pointed tip



The uniquely pointed tip allows you to iron even the hardest to reach areas.

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate. It has great scratch resistancy, glides excellent and is easy to clean.

Smooth gliding

SteamGlide soleplate

Easily removes creases

Steam boost for the most stubborn creases:

100 g/min

Continuous high steam for better crease removal: 35 g/min

Fine spray: Fine spray evenly moistens the fabric

Pointed tip: For ironing tricky areas

Comfortable ironing

360 degree swivel: Provides maximum freedom during ironing

Integrated cord winder for easy storage

Drip-stop

3x easier

Extra-large water inlet

Extra-long cord: 3 m

Extra-clear water level indicator

Fast and powerful ironing

Power for quick heat-up and constant high steam:

2300 W

Technical specifications

Voltage: 220-240 V

Power: 2300 W

Frequency: 50-60 Hz

Dimensions: 328 x 129 x 163 cm

Weight: 1.64 kg

Water tank capacity: 300 ml

Longer living

Double Active Calc System

