

# PHILIPS

## Steam iron

### 3300 series

3m cord

GC3388



## Look hot every day

Great result minimum effort, 3x easier

This Philips steam iron offers you not only extra convenience because of the large water inlet, extra-long cord and water-level indicator; its fashionable design gives you a unique product that is fun and easy to use!

#### **Easily removes creases**

- Extra-large water inlet for fast, easy filling
- Extra-long cord for maximum reach
- Extra-clear indicator for highly visible water level

#### **Smooth gliding**

- SteamGlide soleplate is Philips premium soleplate

#### **Reaches into tricky areas**

- The pointed tip makes ironing along buttons and seams easy

#### **Safe ironing**

- Drip-stop system keeps your garments spotless while ironing

#### **Comfortable ironing**

- Less refilling with extra-large 300 ml water tank
- Double Active Calc System prevents scale build-up

# Highlights

## Extra-large water inlet



With the extra-large water inlet, adding water to your iron is quick and easy. It only takes a few seconds, and there's no more risk of spilling water everywhere!

## Extra-long cord length




With EasyCare's extra-long 3 m cord, you can easily reach right up to the edges of your ironing board – and further!

## Highly visible water level



The extra-clear indicator of your Philips iron, makes the water level highly visible, so you always know if you have enough water at a glance.

## Pointed tip



The pointed tip makes ironing along buttons and seams easy.

## SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.

## Comfortable ironing

**Additional comfort:** 360 degree cord freedom, Extra-clear water level indicator

**Anti-scale management:** Double Active Calc System

**Cord length:** 3 m

**No leakage:** Drip-stop system

**Water tank capacity:** 300 ml

## Crease removal

**Continuous steam:** Up to 35 gr/min

**Reaching tricky areas:** Pointed tip

**Spray**

**Steam Boost:** Up to 95 gr/min

**Vertical Steam**

## Easy to use

**Easy to set up and store:** Extra-large water inlet, Integrated cord storage solution

**Fast heat-up**

## Smooth gliding

**Soleplate:** SteamGlide soleplate

## Technical specifications

**Frequency:** 50-60

**Power:** 2300

**Voltage:** 220 - 240

## Weight and dimensions

**Product dimensions:** 328 x 129 x 163

**Product weight:** 1,64

