

# PHILIPS

## Steam iron

Steam 40g/min;160g steam boost

Ceramic soleplate

Safety Auto Off

2400 Watts

GC3570/32



## Less refilling for longer ironing sessions

With large watertank and safety auto-off

Philips SmoothCare range has one of the largest watertanks there is for steam irons. Iron longer without refilling! Powerful steam will enable you to remove the tough creases easily. Iron switches off automatically when left unattended.

### Comfortable ironing

- Drip-stop system keeps your garments spotless while ironing
- Extra large 400 ml watertank needs less refilling

### Longer lifetime

- Double Active Calc System prevents scale build-up

### Safe ironing

- Iron switches off automatically when left unattended

### Easily removes creases

- Continuous steam output up to 40 g/min
- Steam boost up to 160 g
- Ceramic EasyFlow soleplate

# Highlights

## Double Active Calc System



Double Active Calc system of your Philips steam iron prevents scale build-up through anti scale pills and an easy to use calc clean function.

## Drip-stop system



The Drip Stop system of your Philips steam iron lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

## Up to 40 g/min of steam



Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

## Steam boost up to 160 g



The steam boost can be used for vertical steaming and tough creases.

## Large watertank



Comfortable ironing with less refilling. The 400ml XL water tank allows longer ironing without refilling. The large buttons and comfortable steam slider are easily accessible and give you full control.

## Ceramic EasyFlow soleplate



Ceramic EasyFlow soleplate is scratch resistant, glides well and is easy to clean.

## Automatic shut-off



The iron shuts off automatically when left unattended. If it is left on it's heelrest it will switch off in 8 minutes. When left on the soleplate or on the side, it only takes 30 seconds before the iron shuts off.

# Specifications

## Fast & powerful crease removal

Soleplate: Ceramic soleplate

Continuous steam output: 40 g/min

Steam boost: 160 g

Power: 2400 W

## Easy to use

Water tank capacity: 400 ml

Drip stop

Safety auto off

## Calc management

Calc clean solution: Double active calc clean

## Technical specifications

Voltage: 220-240 V

## Comfortable ironing

Cord length: 2 m

