

PHILIPS

Steam iron

Steam 40g/min; 160g steam boost

Ceramic soleplate

2400 W

Safety Auto Off



GC3580/20



Less refilling for longer ironing sessions

Iron with large water tank

Philips' SmoothCare steam iron range has one of the largest water tanks available for steam irons. Iron for longer without refilling! Powerful steam will enable you to remove tough creases easily.

Comfortable ironing

- Drip-stop system keeps your garments spotless while ironing
- Extra-large 400-ml water tank needs less refilling

Longer lifetime

- Calc-clean to prevent your iron from scale build-up

Easily removes creases

- Continuous steam output up to 40 g/min
- Steam boost up to 160 g
- Ceramic EasyFlow soleplate

Highlights

Drip-stop system



Your Philips steam iron's Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 160 g



The steam boost can be used for vertical steaming and tough creases.

Large water tank



Comfortable ironing with less refilling. The 400-ml XL water tank allows you to iron for longer without refilling. The large buttons and comfortable steam slider are easily accessible and give you full control.

Ceramic EasyFlow soleplate

The Ceramic EasyFlow soleplate is scratch-resistant, glides well and is easy to clean.

Calc-clean



The calc-clean function enables you to simply flush your Philips iron to remove the calc particles from your iron. This will extend the lifetime of your iron.

Specifications

Easy to use

Power cord length: 2 m
 Water tank capacity: 400 ml
 Precision steam tip
 Refill anytime during use
 Safety auto off
 Side-opening door
 Soleplate name: SteamGlide Ceramic

Fast crease removal

Continuous steam: 40 g/min
 Power: 2400 W
 Steam boost: 160 g
 Variable steam levels
 Voltage: 220 V

Scale management

Descaling and cleaning: Self-clean

Storage

Cord storage: Cord clip

Green efficiency

Energy saving*: 20 %

