

# PHILIPS

Handheld garment steamer

Steam&Go

1200 W, up to 22 g/min

Horizontal and Vertical Steaming

70 ml Detachable water tank



GC360/36



## Compact solution for easy de-wrinkling

Use vertically or horizontally for better results

Easier steaming with SmartFlow heated plate. Use vertically or horizontally on difficult-to-iron areas and to refresh clothing - no burns guaranteed. Lightweight and compact design makes it easy to use anytime, anywhere. Just steam and go!

### Quick de-wrinkling

- Vertical and horizontal steaming for more convenience
- SmartFlow heated plate for better steaming results\*
- Automatic continuous steam for easy de-wrinkling
- Brush accessory for thicker fabrics

### Easy to use and safe

- Safe on all ironable fabrics, no burns guaranteed
- No ironing board needed
- Compact design for convenient use, storage and travel
- Detachable water tank for easier filling
- 2.5 m cord for longer reach

### Refreshes clothes without washing or dry cleaning

- Continuous steam removes odours and kills 99.9%\* of bacteria


# Highlights

## Vertical and horizontal steaming



Steam vertically for quick de-wrinkling and to refresh hanging clothes without an ironing board. Steam horizontally to get perfect results on difficult-to-iron areas, like cuffs and collars. In either position, powerful continuous steam provides great results.

## SmartFlow heated plate



Thanks to SmartFlow technology, the steam plate is heated up to an optimal temperature, safe for all fabrics, and prevents wet spots. The heated steam plate helps to press the fabric while steaming horizontally and provides even better steaming results\*.

## Continuous steam



An electric pump automatically provides continuous steam for easy and quick de-wrinkling.

## Brush accessory



The brush attachment opens the fabric fibres and enables better steam penetration. It is especially good for thicker garments like jackets and coats. It can also help to remove dirt and pills.

## Safe on all ironable fabrics



The steamer is safe to use on all ironable fabrics and garments. The steam plate can be safely pressed against any clothing with no risk of burning – a great solution for delicate fabrics, like silk.

## No ironing board needed



Using a clothes steamer on hanging garments eliminates the need for an ironing board, so de-wrinkling is easy and hassle free.

## Ergonomic design



The handheld garment steamer is ergonomically designed to be light, compact and comfortable to use. Just press the trigger and watch wrinkles and creases disappear.

## Detachable water tank




The water tank detaches for easy filling under the tap.

## 2.5 m cord



for longer reach

## 99.9% bacteria-free\*



Hot steam refreshes your clothes and kills up to 99.9% of bacteria\*. Less-frequent washing and dry cleaning saves time and money, and helps clothes last longer.

# Specifications

## Fast crease removal

Continuous steam: Up to 22 g/min

Power: 1200 W

Ready to use: < 1 min

Voltage: 220–240 V

## Easy to use

Safe on all ironable fabrics: Even delicates like silk

Water tank capacity: 70 ml

Detachable water tank

Power cord length: 2.5 m

Ready to use: Light indicator

Refill anytime during use

## Accessories included

Brush

Glove for extra protection

## Size and weight

Packaging dimensions (W x H x D): 38 x 12.8 x 15 cm

## Guarantee

2 year worldwide guarantee

## Green efficiency

Product packaging: 100% recyclable

User manual: 100% recycled paper

