



Handheld garment steamer

- 1200 W, up to 22 g/min
- Horizontal and Vertical Steaming
- 70 ml Detachable water tank

GC360/36

Compact solution for easy de-wrinkling

Use vertically or horizontally for better results

Easier steaming with SmartFlow heated plate. Use vertically or horizontally on difficult-to-iron areas and to refresh clothing - no burns guaranteed. Lightweight and compact design makes it easy to use anytime, anywhere. Just steam and go!

Benefits

Quick de-wrinkling

- Vertical and horizontal steaming for more convenience
- SmartFlow heated plate for better steaming results*
- Automatic continuous steam for easy de-wrinkling
- Brush accessory for thicker fabrics

Easy to use and safe

- Safe on all ironable fabrics, no burns guaranteed
- No ironing board needed

- Compact design for convenient use, storage and travel
- Detachable water tank for easier filling
- 2.5 m cord for longer reach

Refreshes clothes without washing or dry cleaning

- Continuous steam removes odours and kills 99.9%* of bacteria

PHILIPS


Features

Vertical and horizontal steaming



Steam vertically for quick de-wrinkling and to refresh hanging clothes without an ironing board. Steam horizontally to get perfect results on difficult-to-iron areas, like cuffs and collars. In either position, powerful continuous steam provides great results.

SmartFlow heated plate



Thanks to SmartFlow technology, the steam plate is heated up to an optimal temperature, safe for all fabrics, and prevents wet spots. The heated steam plate helps to press the fabric while steaming horizontally and provides even better steaming results*.

Continuous steam



An electric pump automatically provides continuous steam for easy and quick de-wrinkling.

Brush accessory



The brush attachment opens the fabric fibres and enables better steam penetration. It is especially good for thicker garments like jackets and coats. It can also help to remove dirt and pills.

Safe on all ironable fabrics



The steamer is safe to use on all ironable fabrics and garments. The steam plate can be safely pressed against any clothing with no risk of burning – a great solution for delicate fabrics, like silk.

No ironing board needed



Using a clothes steamer on hanging garments eliminates the need for an ironing board, so de-wrinkling is easy and hassle free.

Ergonomic design



The handheld garment steamer is ergonomically designed to be light, compact and comfortable to use. Just press the trigger and watch wrinkles and creases disappear.

Detachable water tank




The water tank detaches for easy filling under the tap.

2.5 m cord



for longer reach

99.9% bacteria-free*



Hot steam refreshes your clothes and kills up to 99.9% of bacteria*. Less-frequent washing and dry cleaning saves time and money, and helps clothes last longer.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

| | |
|------------------|----------------|
| Continuous steam | Up to 22 g/min |
| Power | 1200 W |
| Ready to use | < 1 min |
| Voltage | 220-240 V |

Easy to use

| | |
|------------------------------|--------------------------|
| Safe on all ironable fabrics | Even delicates like silk |
| Water tank capacity | 70 ml |
| Detachable water tank | Yes |
| Power cord length | 2.5 m |
| Ready to use | Light indicator |
| Refill anytime during use | Yes |

Accessories included

| | |
|----------------------------|-----|
| Brush | Yes |
| Glove for extra protection | Yes |

Size and weight

| | |
|----------------------------------|-------------------|
| Packaging dimensions (W x H x D) | 38 x 12.8 x 15 cm |
|----------------------------------|-------------------|

Guarantee

| | |
|----------------------------|-----|
| 2 year worldwide guarantee | Yes |
|----------------------------|-----|

Green efficiency

| | |
|-------------------|---------------------|
| Product packaging | 100% recyclable |
| User manual | 100% recycled paper |

Packaging dimensions

| | |
|-----------------------------|----------------|
| Height | 15.00 cm |
| Width | 38.00 cm |
| Depth | 12.80 cm |
| Net weight | 0.89 kg |
| Gross weight | 1.11 kg |
| EAN | 08710103832089 |
| Number of products included | 1 |
| Country of origin | CN |
| Harmonised Systems Code | 851679 |

Outer Carton

| | |
|-----------------------------|----------------|
| Length | 39.50 cm |
| Width | 27.10 cm |
| Height | 32.00 cm |
| Gross weight | 5.08 kg |
| EAN | 18710103832086 |
| Number of consumer packages | 4 |

* Compared to Philips Steam&Go GC310 and GC320; without SmartFlow heated plate.

* Tested by external body for bacteria types Escherichia coli 8099, Staphylococcus aureus ATCC 6538, Candida albicans ATCC 10231 with 1 minute steaming time.



data subject to change
2018, June 16

Version: 8.0.1
EAN: 08710103832089

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com