

PHILIPS

Steam iron

EnergyCare

Auto Shut Off

GC3660



100% steam power, 20%* less energy

Steam iron for greener results

The innovative feature in the Philips steam iron, makes sure you get the 100% steam power to remove creases thoroughly. At the same time, it saves 20%* energy automatically, because it eliminates wasted steam.

Auto Energy Saving

- Automatic Energy Saving

Comfortable ironing

- 130 g steam boost to remove stubborn creases easily
- Soft grip for lasting ironing comfort

Safe ironing

- Electronic shut-off when iron is left unattended
- Drip-stop system keeps your garments spotless while ironing

Reaches into tricky areas

- Steam tip allows you to have steam in hard-to-reach areas

Longer lifetime

- Double Active Calc System prevents scale build-up




Highlights

Steam tip

The unique steam tip of this Philips iron, combines a particularly pointed front of the soleplate with special elongated steam slots in the tip, to reach right into the smallest and most difficult areas for the best ironing results.

Auto shut-off



The electronic shut-off automatically switches the iron off when it is left unattended or tips over.

Drip-stop system



The Drip Stop system of your Philips steam iron lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Double Active Calc System



Double Active Calc system of your Philips steam iron prevents scale build-up through anti scale pills and an easy to use calc clean function.

Auto Energy Saving

Automatic Energy Saving The innovative feature in the Philips steam iron, makes sure you get the 100% steam power to remove creases thoroughly. At the same time, it saves energy automatically, because it eliminates wasted steam.

Soft grip

The soft handgrip of this Philips iron allows for comfortable ironing even during longer sessions.

Steam boost up to 130 g

The steam boost can be used for vertical steaming and tough creases.

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide
 Continuous steam output: 40 g/min
 Steam boost: 130 g
 Vertical steaming
 Spray
 Steam tip
 Power: 2400 W

Easy to use

Water tank capacity: 300 ml
 Filling and emptying water: Extra large filling hole
 Drip stop
 Soft grip
 Safety auto off
 Cord storage: Cord clip
 Power cord length: 3 m
 Cord freedom (swivel): 180 degree cord freedom

Sustainability

Energy saving: 20% energy reduction

Calc management

Suitable for tap water
 Calc clean solution: Double active calc clean

Technical specifications

Weight of iron: 1.6 kg
 Voltage: 220 - 240 V

