



Steam iron

- 2400 W
- 190 g steam boost
- 35 g/min continuous steam
- Ceramic soleplate

GC3672/26

Cordless ironing for ultimate freedom

EasySpeed Advanced combines powerful steam with the freedom of cordless ironing. Reach anywhere on the board and iron difficult areas with ease. Fast to heat up, quick recharging in seconds and carry lock for storing.

Benefits

Easy ironing

- Durable ceramic soleplate for easy gliding
- Less refilling with extra-large 300 ml water tank
- Carry lock and cord wrapping clip for easy and tidy storage

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Extra-large water hole for fast filling and emptying
- Up to 190 g steam boost blasts stubborn creases
- Smart base recharges in seconds with light-up indicator
- Steam output up to 35 g/min for strong, steady performance

PHILIPS

Features

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank so you can iron more clothes in one go.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Steam boost up to 190 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Easy storage



The iron attaches securely to its base with our carry-lock system. The cord is easily wrapped around the base and held in place with a clip for tidy storage.

Fast-charging base



The smart base unit recharges the iron in seconds. Coloured-light feedback indicates when the iron is ready to use and reminds you when you need to recharge.

Up to 35 g/min of steam



Steam output up to 35 g/min for strong and steady performance

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Continuous steam 35 g/min
Power 2400 W

Steam boost 190 g
Variable steam levels Yes
Vertical steam Yes

EasySpeed Advanced

Water spray	Yes
Heating time	30 sec.

Easy to use

Soleplate name	Ceramic
Water tank capacity	300 ml
Power cord length	1.8 m
Precision steam tip	Yes
Tap water suitable	Yes
Drip-stop	Yes
Extra-large filling hole	Yes

Scale management

Descaling and cleaning	Anti-calc solution
------------------------	--------------------

Storage

Cord storage	Cord clip
--------------	-----------

Size and weight

Weight of iron	1.020 kg
----------------	----------

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

Energy saving mode	Yes
User manual	100% recycled paper

Packaging dimensions

Height	19.00 cm
Width	36.50 cm
Depth	18.50 cm
Net weight	1.70 kg
Gross weight	2.14 kg
EAN	08710103872207
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851640

Outer Carton

Length	38.00 cm
Width	38.00 cm
Height	40.00 cm
Gross weight	9.15 kg
EAN	18710103872204
Number of consumer packages	4



data subject to change
2018, April 28

Version: 1.0.1
EAN: 08710103872207

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com