

PHILIPS

Steam iron


EasySpeed Advanced

2400 W

190 g steam boost

35 g/min continuous steam

Ceramic soleplate



GC3675/36



Cordless ironing for ultimate freedom

EasySpeed Advanced combines powerful steam with the freedom of cordless ironing. Reach anywhere on the board and iron difficult areas with ease. Fast to heat up, quick recharging in seconds and carry lock for storing.

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Up to 190 g steam boost blasts stubborn creases
- Steam output up to 35 g/min for strong, steady performance
- Smart base recharges in seconds with light-up indicator
- Extra-large water hole for fast filling and emptying

Easy ironing

- Automatic shut-off when iron is left unattended
- Durable ceramic soleplate for easy gliding
- Carry lock and cord wrapping clip for easy and tidy storage
- Less refilling with extra-large 300 ml water tank

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

Highlights

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

Steam boost up to 190 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 35 g/min of steam



Steam output up to 35 g/min for strong and steady performance

Fast-charging base



The smart base unit recharges the iron in seconds. Coloured-light feedback indicates when the iron is ready to use and reminds you when you need to recharge.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Automatic shut-off



The iron shuts itself off if you leave it standing still. On its heel rest, it will automatically switch off in 8 minutes. Lying flat, it shuts down after 30 motionless seconds.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Easy storage



The iron attaches securely to its base with our carry-lock system. The cord is easily wrapped around the base and held in place with a clip for tidy storage.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank so you can iron more clothes in one go.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Specifications

Fast crease removal

Continuous steam: 35 g/min
Power: 2400 W
Steam boost: 190 g
Variable steam levels
Vertical steam
Water spray
Heating time: 30 sec.

Easy to use

Soleplate name: Ceramic
Water tank capacity: 300 ml
Power cord length: 1.8 m

Precision steam tip
Tap water suitable
Drip-stop
Extra-large filling hole
Auto shut-off

Scale management

Descaling and cleaning: Anti-calc solution

Storage

Cord storage: Cord clip

Size and weight

Weight of iron: 1.020 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
User manual: 100% recycled paper

