



Steam iron

- 2400 W
- 190 g steam boost
- 35 g/min continuous steam
- Ceramic soleplate

GC3675/36

Cordless ironing for ultimate freedom

EasySpeed Advanced combines powerful steam with the freedom of cordless ironing. Reach anywhere on the board and iron difficult areas with ease. Fast to heat up, quick recharging in seconds and carry lock for storing.

Benefits

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Up to 190 g steam boost blasts stubborn creases
- Steam output up to 35 g/min for strong, steady performance
- Smart base recharges in seconds with light-up indicator
- Extra-large water hole for fast filling and emptying

Easy ironing

- Automatic shut-off when iron is left unattended

- Durable ceramic soleplate for easy gliding
- Carry lock and cord wrapping clip for easy and tidy storage
- Less refilling with extra-large 300 ml water tank

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

PHILIPS

Features

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

Steam boost up to 190 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 35 g/min of steam



Steam output up to 35 g/min for strong and steady performance

Fast-charging base



The smart base unit recharges the iron in seconds. Coloured-light feedback indicates when the iron is ready to use and reminds you when you need to recharge.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Automatic shut-off



The iron shuts itself off if you leave it standing still. On its heel rest, it will automatically switch off in 8 minutes. Lying flat, it shuts down after 30 motionless seconds.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Easy storage



The iron attaches securely to its base with our carry-lock system. The cord is easily wrapped around the base and held in place with a clip for tidy storage.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank so you can iron more clothes in one go.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Continuous steam 35 g/min

Power 2400 W
Steam boost 190 g

EasySpeed Advanced

Variable steam levels	Yes
Vertical steam	Yes
Water spray	Yes
Heating time	30 sec.

Easy to use

Soleplate name	Ceramic
Water tank capacity	300 ml
Power cord length	1.8 m
Precision steam tip	Yes
Tap water suitable	Yes
Drip-stop	Yes
Extra-large filling hole	Yes
Auto shut-off	Yes

Scale management

Descaling and cleaning	Anti-calc solution
------------------------	--------------------

Storage

Cord storage	Cord clip
--------------	-----------

Size and weight

Weight of iron	1.020 kg
----------------	----------

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

Energy saving mode	Yes
User manual	100% recycled paper

Packaging dimensions

Height	19.00 cm
Width	36.50 cm
Depth	18.50 cm
Net weight	1.61 kg
Gross weight	2.06 kg
EAN	08710103859116
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851640

Outer Carton

Length	38.00 cm
Width	37.50 cm
Height	40.00 cm
Gross weight	8.81 kg
EAN	18710103859113
Number of consumer packages	4



data subject to change
2018, July 13

Version: 3.1.1
EAN: 08710103859116

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com