

PHILIPS

Steam iron

EcoCare

Safety auto off



GC3760



100% steam power, 25%* less energy.

with Auto Energy Saving and 30% recycled material

The innovative feature of this Philips steam iron, makes sure you get 100% steam power to remove creases thoroughly. At the same time it saves 25%* energy, because it reduces wasted steam. 30% of plastic and of Aluminum in iron is recycled.

Comfortable ironing

- Soft grip for lasting ironing comfort
- Steam boost up to 160 g

Longer lifetime

- Double Active Calc System prevents scale build-up

Reaches into tricky areas

- Steam tip allows you to have steam in hard-to-reach areas

Safe ironing

- Drip-stop system keeps your garments spotless while ironing
- Automatically turned off for safety and energy saving

Auto Energy Saving

- Automatic Energy Saving



asimpleswitch.com

Highlights

Double Active Calc System




Double Active Calc system of your Philips steam iron prevents scale build-up through anti scale pills and an easy to use calc clean function.

Soft grip

The soft handgrip of this Philips iron allows for comfortable ironing even during longer sessions.

Steam tip



The unique steam tip of this Philips iron, combines a particularly pointed front of the soleplate with special elongated steam slots in the tip, to reach right into the smallest and most difficult areas for the best ironing results.

Drip-stop system



The Drip Stop system of your Philips steam iron lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Auto Energy Saving



Automatic Energy Saving The innovative feature in the Philips steam iron, makes sure you get the 100% steam power to remove creases thoroughly. At the same time, it saves energy automatically, because it eliminates wasted steam.

Safety auto off



The safety auto off function automatically switches off the appliance if it has not been used for 5 minutes, to save energy.

Steam boost up to 160 g



The steam boost can be used for vertical steaming and tough creases.

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide
 Continuous steam output: 40 g/min
 Steam boost: 160 g
 Vertical steaming
 Spray
 Steam tip
 Power: 2400 W

Easy to use

Water tank capacity: 300 ml
 Filling and emptying water: Extra large filling hole
 Drip stop
 Soft grip
 Safety auto off
 Cord storage: Cord clip
 Power cord length: 2.5 m
 Cord freedom (swivel): 180 degree cord freedom

Sustainability

Energy saving: 25% energy reduction
 Recycled materials: 30 %

Calc management

Suitable for tap water
 Calc clean solution: Double active calc clean

Technical specifications

Weight of iron: 1.6 kg
 Voltage: 220 - 240 V



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

