

PHILIPS

Steam iron

Azur Performer


Steam 40g/min; 140g steam boost

SteamGlide soleplate

Anti-calc

2400 Watts

GC3802/20



Faster, Easier and Smarter

With our innovative steam and temperature control

The Philips steam iron Azur Performer combines powerful performance with ease of use. Our Auto Steam Control provides the right amount of steam for each garment. The SteamGlide soleplate delivers great gliding to speed up your ironing.

Fast and powerful performance

- 2400 W for quick iron heat-up
- Steam output of up to 40 g/min for better crease removal
- Steam boost up to 140 g

Easy gliding on all fabrics

- SteamGlide soleplate for smooth and easy gliding

Safe ironing

- Double Active Calc System to help prevent calc build-up

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Triple precision tip for optimal control and visibility
- Optimal weight for easier manoeuvrability over your garments



asimpleswitch.com

Highlights

2400 W for quick heat-up



With 2400 W, the Azur Performer Plus steam iron will heat up quickly and give a powerful performance to deliver super ironing results.

Steam up to 40 g/min



Continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 140 g



Steam boost up to 140 g for fast removal of even the most stubborn creases.

SteamGlide soleplate



The SteamGlide soleplate on the Azur Performer steam iron provides a premium gliding experience, great scratch resistance and easy cleaning.

Double Active Calc Clean



Your Philips steam iron's Double Active Calc Clean system prevents scale build-up through anti-scale pills and an easy-to-use calc clean function. Regular cleaning of calc from your steam iron results in fewer white stains from calc and longer steam performance, giving better ironing results.

Auto Steam Control



Auto Steam Control takes away the worry of selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, a button groove and a sleek nose design. The Triple Precision tip enables you to reach into even the trickiest areas, e.g. around buttons or between pleats.

Optimal weight



The iron has an optimal weight for moving easily over any garment, making ironing less of a hassle and making it easy to move the iron constantly between the board and its heel rest.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide
Continuous steam output: 40 g/min
Steam boost: 140 g
Vertical steaming
Spray
Power: 2400 W

Comfortable ironing

Cord length: 2 m

Easy to use

Water tank capacity: 300 ml
Filling and emptying water: Side-opening door
Drip stop
Soft grip
Cord storage: Cord clip

Power cord length: 2 m

Reaching tricky areas: Triple precision tip
Fast and easy filling

Sustainability

ECO setting: 20% energy reduction

Calc management

Calc clean solution: Double active calc clean

