

PHILIPS

Steam iron

Azur Performer


Steam 40g/min; 160g steam boost

SteamGlide Plus soleplate

Anti-calc

2400 Watts

GC3811/70



Faster, Easier and Smarter

With our innovative steam and temperature control

The Philips steam iron Azur Performer combines powerful performance with ease of use. Our Auto Steam Control gives the right amount of steam with each garment. The SteamGlide Plus soleplate will wizz through your ironing.

Fast and powerful performance

- 2400W for quick iron heat up
- Steam output of up to 40 g/min for better crease removal
- Steam boost up to 160 g

Easy gliding on all fabrics

- SteamGlide Plus soleplate: Our best gliding, faster ironing

Safe ironing

- Double Active Calc System to help prevent calc built-up

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Triple precision tip for optimal control and visibility
- Optimal weight for easier manoeuvrability over your garments



asimpleswitch.com

Highlights

2400W for quick heat up



With the 2400W the Azur Performer Plus steam iron will heat up quickly and give a powerful performance to deliver super ironing results.

Steam up to 40 g/min



Continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 160 g



The steam boost can be used for vertical steaming and tough creases.

SteamGlide Plus soleplate



Our best gliding SteamGlide Plus soleplate to whizz through your ironing. The carefully designed vents secure a well balanced steam distribution.

Double Active Calc Clean




The Double Active Calc system of your Philips steam iron prevents scale build-up through anti-scale pills and an easy-to-use calc clean function. Regular cleaning of your steam iron from calc results in less white stains from calc and longer steam performance giving better ironing results.

Auto Steam Control



Auto Steam Control takes away your worry for selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. The Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

Optimal weight



The iron has the optimal weight to move easily over any garment, making ironing less of a hassle and easy to constantly place the iron on the board and back to its heel rest.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide Plus

Continuous steam output: 40 g/min

Steam boost: 160 g

Vertical steaming

Spray

Power: 2400 W

Comfortable ironing

Cord length: 2 m

Easy to use

Water tank capacity: 300 ml

Filling and emptying water: Sideways opening door

Drip stop

Cord storage: Cord clip

Power cord length: 2 m

Reaching tricky areas: Triple precision tip

Fast and easy filling

Textured handle

Sustainability

ECO setting: 20% energy reduction

Calc management

Calc clean solution: Double active calc clean

