

PHILIPS

Steam iron

Azur Performer

Steam 45 g/min; 200 g steam boost

SteamGlide soleplate

Anti-calc

2600 Watts

GC3829/80



Faster, Easier and Smarter

With our innovative steam and temperature control

The Philips steam iron Azur Performer combines powerful performance with ease of use. Our Auto Steam Control provides the right amount of steam for each garment. The SteamGlide soleplate will whizz through your ironing.

Easy gliding on all fabrics

- SteamGlide soleplate for smooth and easy gliding

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Optimal weight for easier manoeuvrability over your garments
- Triple precision tip for optimal control and visibility

Safe ironing

- Self-Clean for effective calc removal

Fast and powerful performance

- 2600 W for quick heat-up and powerful performance
- Steam output of up to 45 g/min for better crease removal
- Steam boost up to 200 g



asimpleswitch.com

Highlights

2600 W for quick heat-up



2600 W for quick heat-up and powerful performance.

Steam up to 45 g/min



Continuous steam output of up to 45 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

Auto Steam Control



Auto Steam Control takes away the worry of selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Optimal weight



The iron has an optimal weight for moving easily over any garment, making ironing less of a hassle and making it easy to move the iron constantly between the board and its heel rest.

SteamGlide soleplate



The SteamGlide soleplate on the Azur Performer steam iron provides a premium gliding experience, great scratch resistance and easy cleaning.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, a button groove and a sleek nose design. The Triple Precision tip enables you to reach into even the trickiest areas, e.g. around buttons or between pleats.

Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide
Continuous steam output: 45 g/min
Steam boost: 200 g
Vertical steaming
Spray
Power: 2600 W

Easy to use

Water tank capacity: 300 ml
Filling and emptying water: Side-opening door
Drip stop
Power cord length: 2 m
Reaching tricky areas: Triple precision tip
Fast and easy filling
Textured handle

Sustainability

ECO setting: 20% energy reduction

Calc management

Calc clean solution: Self-clean

Comfortable ironing

Cord length: 2 m

