

Garment Care range 2001



GC 6006/6007



GC 6004/6005



GC 6002



GC 6000



HI 985



HI 981



GC 4040



GC 4035



GC 4030



GC 4025



GC 4020



GC 4015



GC 4010



GC 4005

PROVAPOR

	Azur GC 6007	Azur GC 6006	Vario Elance GC 6005	Vario Elance GC 6004	Inox Elance GC 6002	Elance GC 6000
Technical data						
Power (W)	Iron 800 Boiler 1200	Iron 800 Boiler 1200	Iron 800 Boiler 1200	Iron 800 Boiler 1200	Iron 800 Boiler 1200	Iron 800 Boiler 1200
Voltage (V)	220-240	220-240	220-240	220-240	220-240	220-240
Dimensions (mm)						
Iron	370x240x270	370x240x270	370x240x270	370x240x270	370x240x270	370x240x270
F-box	220x390x390	220x390x390	220x390x390	220x390x390	220x390x390	220x390x390
A-box	na	na	na	na	na	na
Pieces per unit	1	1	1	1	1	1
Weight iron (gr)	4800	4800	4800	4800	4800	4800
Pallet capacity	54	54	54	54	54	54

	Anodilium	Anodilium	Optinox	Optinox	Optinox	Optinox
Features						
Soleplate	Anodilium	Anodilium	Optinox	Optinox	Optinox	Optinox
Steam						
- Variable steam	●	●	●	●	-	-
- Steam output (gr)	80	80	80	80	70	60
- Positions (incl. 0 pos)	6	6	stepless/cont.*	stepless/cont.*	na	na
Spray mist	●	●	-	-	-	-
Shot of steam (gr)	●	●	-	-	-	-
Vertical shot of steam	perm. vert. steam	perm. vert. steam	perm. vert. steam	perm. vert. steam	perm. vert. steam	perm. vert. steam
Turbo steam	-	-	-	-	-	-
Water						
Contents (ml)	1000	1000	1000	1000	1000	1000
Visible	-	-	-	-	-	-
Spray	-	-	-	-	-	-
Drip stop	na	na	na	na	na	na
Detachable Tank	-	-	-	-	-	-
Anti Calc						
Anti Calc Formula	●	-	●	-	-	-
Calc Clean	-	-	-	-	-	-
Others						
Cord length (m)	1.8	1.8	1.8	1.8	1.8	1.8
Cordwinder	-	-	-	-	-	-
Pilot lamp	●	●	●	●	●	●
Soft touch	●	●	-	-	-	-
Auto Shut Off	-	-	-	-	-	-
Swivel (degrees)	360	360	180	180	180	180
Soleplate cover	-	-	-	-	-	-
Carry case	-	-	-	-	-	-
Boiler material	inox	inox	inox	inox	inox	aluminium
Pressure	3.5 bar	3.5 bar	3.5 bar	3.5 bar	3 bar	2.5 bar
Boiler ready light	●	●	●	●	-	-
Boiler empty light	●	●	-	-	-	-
De-pressurize function	●	●	●	●	●	●
			* on boiler			

SUPERVAPOR

	HI985	HI981
Technical data		
Power (W)	Iron 800 Boiler 1000	Iron 800 Boiler 1000
Voltage (V)	220-240	220-240
Dimensions (mm)		
Iron	330x290x200	330x290x200
F-box	220x390x390	220x390x390
A-box	-	-
Pieces per unit	1	1
Weight iron (gr)	6150	6150
Pallet capacity	54	54

	Aluminium	Aluminium
Features		
Soleplate	Aluminium	Aluminium
Steam		
- Variable steam	●	-
- Steam output (gr)	70	70
- Positions (incl. 0 pos)	5	na
Spray mist	-	-
Shot of steam (gr)	-	-
Vertical shot of steam	perm. vert. steam	perm. vert. steam
Turbo steam	-	-
Water		
Contents (ml)	1000	1000
Visible	-	-
Spray	-	-
Drip stop	na	na
Detachable Tank	-	-
Anti Calc		
Anti Calc Formula	-	-
Calc Clean	-	-
Others		
Cord length (m)	2.0	2.0
Cordwinder	clip	clip
Pilot lamp	●	●
Soft touch	cork	cork
Auto Shut Off	-	-
Swivel (degrees)	180	180
Soleplate cover	-	-
Carry case	-	-
Boiler material	aluminium	aluminium
Pressure	2 bar	2 bar
Boiler ready light	●	●
Boiler empty light	●	●
De-pressurize function	●	●
Removable tray	●	●
Manometer	●	-

AZUR 4000

	GC4040	GC4035	GC4030	GC4025	GC4020	GC4015	GC4010	GC4005
Technical data								
Power (W)	2200	2200	2200	2200	2200	2200	2200	2200
Voltage (V)	220-240	220-240	220-240	220-240	220-240	220-240	220-240	220-240
Dimensions (mm)								
Iron	309x134x167	303x120x151	303x120x151	309x134x167	303x120x151	303x120x151	303x120x151	303x120x151
F-box	328x143x181	328x129x163	328x129x163	328x143x181	328x129x163	328x129x163	328x129x163	328x129x163
A-box	460x345x392	419x345x357	419x345x357	460x345x392	419x345x357	419x345x357	419x345x357	419x345x357
Pieces per unit	6	6	6	6	6	6	6	6
Weight iron (gr)	1650	1470	1470	1650	1470	1470	1470	1470
Pallet capacity	150	216	216	150	216	216	216	216

	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™
Features								
Soleplate	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™	Carezza™
Steam								
- Variable steam								
- Steam output (gr)	0-40	0-40	0-40	0-40	0-40	0-40	0-40	0-40
- Positions (incl. 0 pos)	7	7	7	7	7	7	7	7
Spray mist	-	-	-	-	-	-	-	-
Shot of steam (gr)	80	80	80	80	80	80	80	80
Vertical shot of steam	●	●	●	●	●	●	●	-
Turbo steam	-	-	-	-	-	-	-	-
Water								
Contents (ml)	350	350	350	350	350	350	350	350
Visible	●	●	●	●	●	●	●	●
Spray	●	●	●	●	●	●	●	●
Drip stop	●	●	●	●	●	●	●	●
Detachable Tank	-	-	-	-	-	-	-	-
Anti Calc								
Permanent Anti Calc Formula	●	●	●	●	●	●	-	-
Self/Calc-Clean	●	●	●	●	●	●	●	●
Others								
Cord length (m)	3.0	2.4	2.4	2.4	2.4	2.4	2.4	2.4
Cordwinder	●	●	●	●	●	●	●	●
Pilot lamp	●	●	●	●	●	●	●	●
Soft touch	●	●	●	●	●	●	-	-
Auto Shut Off	●	●	●	●	●	●	-	-
Swivel (degrees)	360(ball)	360(ball)	360(ball)	360(ball)	360(ball)	360(ball)	360(ball)	360(ball)
Soleplate cover	●	-	-	●	-	-	-	-
Carry case	-	-	-	-	-	-	-	-

PROVAPOR
SUPERVAPOR
AZUR 4000
AZUR EXCEL PLUS
ELANCE PLUS
MISTRAL
COMFORT



PHILIPS

Let's make things better.

