

# PHILIPS

Compact garment steamer

CompactTouch

1200-1400w (220-240v)

3 steam levels

Integrated cover for storage

Door hanger, glove



GC430/05



## Revive your delicate clothes with steam Designed for easier storage

Compact yet powerful. The new Philips CompactTouch garment steamer is specially designed to combine powerful steam performance with a super compact design so that you can refresh your clothes without much hassle.

### Quick crease removal

- Powerful continuous steam
- 3 steam levels

### Easy to use

- Easy garment hanger
- Large water tank for longer use
- Auto-clean function for longer lifetime

### Easy storage

- Integrated cover for easier storage

### Refreshes clothes without washing or dry cleaning

- Steam kills up to 99.9% of bacteria\*
- Removes cigarette, food and body odors



# Highlights

## Powerful continuous steam



Powerful continuous steam is blown through the nozzles, enabling you to remove creases with only a few strokes.

## 3 steam levels



Set your preferred steam level for optimal results on different kinds of garments.

## Integrated storage



The compact integrated design with cover provides enough space to store all the parts including the power cord and the hose inside the base, protecting against dust and helps keeping your home neat and tidy.

## Easy garment hanger



Easy garment hanger accessory lets you hang your garments on a door while steaming.

## Large water tank



600 ml large water tank creates enough steam for steaming up to 30 mins.

## Auto-clean



The Auto-clean function flushes the steamer to remove the calc particles and residues. This will extend the lifetime of your steamer.

# Specifications

## Fast & powerful crease removal

Steam output control: 3 settings  
Power: 1200-1400 W  
Steam on demand technology

## Easy to use

Water tank capacity: 600 ml  
Refill any time  
Safety auto off  
Cord storage  
Power cord length: 1.8 m  
Hose length: 1.6 m  
Safe for all fabrics: Even for delicates like silks  
Heat up time: <1 min

## Calc management

Suitable for tap water  
Calc clean solution: Anti-calc solution, Auto-clean

## Accessories

Glove for extra protection  
Integrated cover  
Easy garment hanger

## Technical specifications

Product dimensions: 38.2 x 19.8 x 11.1 cm  
Packaging dimensions: 41.5 x 23.5 x 15.0 cm  
Voltage: 220-240 V  
Weight of product: 1.59 kg  
Weight of product with package: 2.14 kg

