

PHILIPS

Handheld garment steamer

1500 W, up to 30 g/min

PureSteam technology

XL water tank

2-in-1 function



GC440/27



Your new wardrobe Essential

Ideal for quick touch-ups and delicate clothes

Thanks to the innovative PureSteam Technology and quick calc release, the new StyleTouch garment steamer ensures powerful steam performance for years to come! Quick, safe & easy, it is perfect for last minute ironing and delicate clothes.

Quick and powerful crease removal

- More powerful steam up to 30g/min for faster results
- PureSteam technology for consistent powerful steam over time
- 2-in-1 vertical & horizontal steaming for better results
- Ready in 60 seconds

Easy to use & safe

- Quick calc release
- Large water tank for longer steaming
- Automatic continuous steam delivered by electric pump
- SmartFlow heated plate to prevent wet spots
- Safe to use on all delicate fabrics like silk
- Safe resting position on base

Refresh clothes without washing or dry cleaning

- Powerful steam removes odors and kills 99,9% of the bacteria

Highlights

PureSteam technology



PureSteam technology is an innovative technology that prevents calc from building up around the steamer's engine. It enables consistent powerful steam for years to come.

2-in-1 function



The 2-in-1 function enables both vertical and horizontal steaming. When steaming horizontally on a flat surface, you can achieve better results especially on tricky areas like collars and cuffs.

Quick calc release



Thanks to the quick calc release, your appliance can last for longer with the same steam performance.

XL water tank



The 200 ml water tank enables steaming up to 3 garments in one go. Enough for your quick touch ups before leaving the house!

Continuous steam



Thanks to the electric pump, you do not need to pump manually. Just hold the trigger pressed and steam comes continuously.

SmartFlow heated plate



The SmartFlow heated plate prevents condensation on your garments while still being 100% safe on all your clothes even delicates.

Safe on all garments



The steamer is safe to use on all fabrics. It is a great solution for delicate fabrics like silk and cashmere.

Safe rest



You can rest the garment steamer just by making it stand on its base. It is a very easy and safe resting position.

Remove odors & bacteria



Powerful steam removes cigarette, food and body odors. Steam also kills 99,9% of the bacteria. *

Specifications

Technology

PureSteam Technology

Fast crease removal

2-in-1 function

Continuous steam: Up to 30 g/min

Power: 1500 W

Ready to use: 1 min

Steam-on-demand

Vertical steam

Voltage: 240 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk

Water tank capacity: 200 ml

Power cord length: 2 m

Ready to use: Light indicator

Refill any time during use

Tap water suitable

On/off switch

Scale management

Descaling and cleaning: Built-in calc container

Accessories included

Brush

Size and weight

Packaging dimensions (WxHxL): 32 x 22 x 17 cm

Product dimensions (WxHxL): 30 x 17 x 13 cm

Total weight with packaging: 0,9 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Product packaging: 100% recycable

User manual: 100% recycled paper

Design

Color: Blue

