

PHILIPS

Garment Steamer


1500 W, up to 30 g/min

2-in-1 function

PureSteam technology

StyleMat

GC442/47



Most powerful steam for quicker results every day

With innovative PureSteam technology and StyleMat

Thanks to the innovative PureSteam technology with quick calc release, StyleTouch Pure garment steamer delivers powerful steam for years to come. Effectively eliminating creases and easy to use, StyleTouch Pure gets you ready in no time!

Powerful crease removal for years to come

- 2-in-1 vertical and horizontal steaming for better results
- Most powerful steam up to 30g/min for faster results
- PureSteam technology: powerful steam for years to come
- SmartFlow heated plate to prevent wet spots
- StyleMat provides support for final crisp touch
- Ready in 60 seconds

Easy to use and safe

- Quick calc release to remove scale from your steamer
- XL water tank for carefree steaming without refill
- Automatic continuous steam delivered by electric pump
- Brush accessory for thicker fabrics
- Safe to use on all delicate fabrics like silk
- Safe rest during steaming

Refresh clothes without washing or dry cleaning

Highlights

PureSteam technology



Other steamers are easy to lose steam performance over time due to scale build-up. Thanks to the innovative PureSteam technology with quick calc release, the scale does not stick to the heater and is easy to remove. It is so effective that the steam is powerful for years to come.

2-in-1 function



Steam your clothes vertically without using an ironing board, or give them a finishing crisp touch by steaming horizontally on any straight surface around you. Due to its unique internal design this steamer will generate powerful continuous steam even in horizontal position. Especially useful for tricky areas, like collars or cuffs.

Quick calc release



Quick calc release is the easiest way to remove scale from your steamer. Together with PureSteam technology, quick calc release guarantees consistently powerful steam for years to come.

XL watertank



The 200 ml water tank enables steaming up to 3 garments without refill. Enough to touch up a complete outfit and get ready in no time.

Brush accessory



The brush attachment opens the fabric fibers and enables better steam penetration. It is especially good for thicker garments like jackets and coats. It can also help remove dirt and pills.

Continuous steam



Thanks to the electric pump, you do not need to pump manually. Just hold the trigger pressed and steam comes out continuously.

SmartFlow heated plate



The SmartFlow heated plate prevents condensation on your garments while still being 100% safe on all your clothes even delicates.

Safe on all garments



The steamer is safe to use on all fabrics. It is a great solution for delicate fabrics like silk and cashmere.

Safe rest



During the steaming session, you can rest the garment steamer just by letting it stand on its base. It is an easy and safe resting position.

Specifications

Technology

PureSteam Technology

Fast crease removal

Continuous steam: Up to 30 g/min

Power: 1500 W

Ready to use: 1 min

Steam-on-demand

Voltage: 240 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk

Water tank capacity: 200 ml

Power cord length: 2 m

Ready to use: Light indicator

Refill any time during use

Tap water suitable

On/off switch

Scale management

Descaling and cleaning: Built-in calc container

Accessories included

Brush

StyleMat

Size and weight

Packaging dimensions (WxHxL): 32 x 22 x 17 cm

Product dimensions (WxHxL): 30 x 17 x 13 cm

Total weight with packaging: 0,9 kg

Guarantee

2 year worldwide guarantee

Design

Color: Pink

