

PHILIPS

Steam iron

Azur Performer Plus

Steam 45g/min;170g steam boost

SteamGlide Plus soleplate

Anti-calc

2400 Watts



GC4510/36



Faster, Easier and Smarter

With easy calc clean system

The Philips steam iron Azur Performer combines powerful performance with ease of use. The Quick Calc Release for easy de-calc, Auto Steam Control and SteamGlide Plus soleplate, this iron delivers long lasting steam performance.

Easy gliding on all fabrics

- SteamGlide Plus soleplate: Our best gliding, faster ironing

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Optimal weight for easier manoeuvrability over your garments
- Triple precision tip for optimal control and visibility

Safe ironing

- Self-Clean for effective calc removal
- Quick calc release to remove scale from your steamer

Fast and powerful performance

- Steam output of up to 45 g/min for better crease removal
- 2400W for quick iron heat up
- Steam boost up to 170 g

Highlights

Steam up to 45 g/min



Continuous steam output of up to 45 g/min gives you the perfect amount of steam to efficiently remove all creases.

Auto Steam Control




Auto Steam Control takes away your worry for selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Optimal weight



The iron has the optimal weight to move easily over any garment, making ironing less of a hassle and easy to constantly place the iron on the board and back to its heel rest.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. The Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

2400W for quick heat up



With the 2400W the Azur Performer Plus steam iron will heat up quickly and give a powerful performance to deliver super ironing results.

SteamGlide Plus soleplate



Our best gliding SteamGlide Plus soleplate to whizz through your ironing. The carefully designed vents secure a well balanced steam distribution.

Steam boost up to 170 g



The steam boost can be used for vertical steaming and tough creases.

Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

Quick calc release



Quick calc release is the easiest way to remove scale from your iron and guarantees consistently powerful steam for years to come.

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide Plus
Continuous steam output: 45 g/min
Steam boost: 170 g
Vertical steaming
Spray
Power: 2400 W
Ionic deep steam
Variable steam settings

Easy to use

Water tank capacity: 300 ml
Filling and emptying water: Sideways opening door
Drip stop
Cord storage: Cord clip
Power cord length: 2 m
Reaching tricky areas: Triple precision tip
Textured handle

Sustainability

ECO setting: 20% energy reduction

Calc management

Calc clean solution: Self clean
Quick Calc Release

