

PHILIPS

Steam iron

Azur Performer Plus

Steam 45g/min; 180g steam boost

SteamGlide Plus soleplate

Anti-calc

2400 Watts



GC4511/20



Faster, Easier and Smarter

With easy calc clean system

The Philips steam iron Azur Performer combines powerful performance with ease of use. With the Quick Calc Release for easy de-calc, Auto Steam Control and SteamGlide Plus soleplate, this iron delivers long-lasting steam performance.

Fast and powerful performance

- 2400 W for quick iron heat-up
- Steam output of up to 45 g/min for better crease removal
- Steam boost up to 180 g

Easy gliding on all fabrics

- SteamGlide Plus soleplate: Our best gliding, faster ironing

Safe ironing

- Self-Clean for effective calc removal
- Quick calc release to remove scale from your steamer

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Triple precision tip for optimal control and visibility
- Optimal weight for easier manoeuvrability over your garments



asimpleswitch.com

Highlights

2400 W for quick heat-up



With 2400 W, the Azur Performer Plus steam iron will heat up quickly and give a powerful performance to deliver super ironing results.

Steam up to 45 g/min



Continuous steam output of up to 45 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 180 g



The steam boost can be used for vertical steaming and tough creases.

SteamGlide Plus soleplate



Our best-gliding SteamGlide Plus soleplate to whizz through your ironing. The carefully designed vents ensure a well-balanced steam distribution.

Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

Auto Steam Control



Auto Steam Control takes away the worry of selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, a button groove and a sleek nose design. The Triple Precision tip enables you to reach into even the trickiest areas, e.g. around buttons or between pleats.

Optimal weight



The iron has an optimal weight for moving easily over any garment, making ironing less of a hassle and making it easy to move the iron constantly between the board and its heel rest.

Quick calc release



Quick calc release is the easiest way to remove scale from your iron and guarantees consistently powerful steam for years to come.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide Plus
Continuous steam output: 45 g/min
Steam boost: 180 g
Vertical steaming
Spray
Power: 2400 W
Variable steam settings

Comfortable ironing

Cord length: 2 m

Easy to use

Water tank capacity: 300 ml
Filling and emptying water: Side-opening door
Drip stop
Cord storage: Cord clip
Power cord length: 2 m

Reaching tricky areas: Triple precision tip
Fast and easy filling
Textured handle

Sustainability

ECO setting: 20% energy reduction

Calc management

Calc clean solution: Self-clean
Quick Calc Release

