

# PHILIPS

## Steam iron

### Azur Performer Plus

Steam 50g/min; 200g steam boost

T-ionicGlide soleplate

Safety Auto off + Anti-calc

2600 Watts



GC4521/17



## Faster, Easier and Smarter

With our best gliding soleplate yet

The Philips steam iron Azur Performer combines powerful performance with ease of use. Combining easy Quick Calc Release with our 5-star-rated best-gliding T-ionicGlide soleplate and Safety Auto Off to give optimal ironing results, easily.

#### Easy gliding on all fabrics

- T-ionicGlide: our best 5-star rated soleplate

#### Comfortable ironing

- Innovative CordGuide
- Auto Steam Control for the right steam for each garment
- Optimal weight for easier manoeuvrability over your garments
- Triple precision tip for optimal control and visibility

#### Safe ironing

- Iron switches off automatically when left unattended
- Self-Clean for effective calc removal
- Quick calc release to remove scale from your steamer

#### Fast and powerful performance

- 2600 W for quick heat-up and powerful performance
- Steam output of up to 50 g/min for better crease removal
- Steam boost up to 200 g

# Highlights

## 2600 W for quick heat-up



2600 W for quick heat-up and powerful performance.

## Steam up to 50 g/min

Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

## Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

## T-ionicGlide soleplate

T-ionicGlide is Philips' premium soleplate. Delivering a new standard in glide and scratch-resistance for OptimalTemp irons. The patented new coating will secure excellent results. The carefully designed shape and vent holes provide even steam distribution for easy crease removal with the steam iron.

## Safety auto off



The steam iron shuts off automatically when left unattended. It will switch off after 8 minutes when left standing on its heel rest and after 30 seconds when left resting on its soleplate or sides.

## Auto Steam Control



Auto Steam Control takes away the worry of selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

## Optimal weight



The iron has an optimal weight for moving easily over any garment, making ironing less of a hassle and making it easy to move the iron constantly between the board and its heel rest.

## Triple Precision Tip

The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, a button groove and a sleek nose design. The Triple Precision tip enables you to reach into even the trickiest areas, e.g. around buttons or between pleats.

## Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

## CordGuide

The innovative CordGuide simply clicks onto your ironing board and guides the cord away while you iron.

## Quick calc release



Quick calc release is the easiest way to remove scale from your iron and guarantees consistently powerful steam for years to come.

# Specifications

## Accessories

CordGuide

## Calc management

Calc clean solution: Self-clean

Quick Calc Release

## Easy to use

Cord storage: Cord clip

Drip stop

Power cord length: 2.5 m

Safety auto off

Soft grip

Water tank capacity: 300 ml

Filling and emptying water: Side-opening door

## Fast and powerful crease removal

Continuous steam output: 50 g/min

Power: 2600 W

Soleplate: T-ionicGlide

Spray

Steam boost: 200 g

Vertical steaming

Ionic deep steam

Variable steam settings

