

PHILIPS

Steam iron

Azur Performer Plus

Steam 45g/min; 200g steam boost

T-ionicGlide soleplate

Safety Auto off + Anti-calc

2400 Watts

GC4523/10



Faster, Easier and Smarter

With our best gliding soleplate yet

The Philips steam iron Azur Performer combines powerful performance with ease of use. Combining easy Quick Calc Release with our 5-star rated, best gliding T-ionicGlide soleplate and Safety Auto Off to give optimal ironing results, easily.

Easy gliding on all fabrics

- T-ionicGlide: our best 5-star rated soleplate

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Optimal weight for easier manoeuvrability over your garments
- Triple precision tip for optimal control and visibility

Safe ironing

- Iron switches off automatically when left unattended
- Self-Clean for effective calc removal
- Quick calc release to remove scale from your steamer

Fast and powerful performance

- 2400 W for quick heat up
- Steam output of up to 45 g/min for better crease removal
- Steam boost up to 200 g

Highlights

2400 W for quick heat up



2400 W for quick heat up and powerful performance

Steam up to 45 g/min



Continuous steam output of up to 45 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

T-ionicGlide soleplate



T-ionicGlide is Philips most premium soleplate. Delivering a new standard in glide and scratch resistance for OptimalTemp irons.

The patented new coating will secure excellent results. The carefully designed shape and vent holes provide an even steam distribution for easy crease removal with the steam iron.

Automatic shut-off



The steam iron shuts off automatically when left unattended. It will switch off after 8 minutes when left standing on its heelrest and after 30 seconds when left resting on its soleplate or sides.

Auto Steam Control




Auto Steam Control takes away your worry for selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Optimal weight



The iron has the optimal weight to move easily over any garment, making ironing less of a hassle and easy to constantly place the iron on the board and back to its heel rest.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. The Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

Quick calc release



Quick calc release is the easiest way to remove scale from your iron and guarantees consistently powerful steam for years to come.

Specifications

Calc management

Calc clean solution: Self clean
Quick Calc Release

Easy to use

Cord storage: Cord clip
Drip stop
Power cord length: 2.5 m
Safety auto off

Soft grip

Water tank capacity: 300 ml
Filling and emptying water: Sideways opening door

Fast & powerful crease removal

Continuous steam output: 45 g/min
Power: 2400 W
Soleplate: T-ionicGlide

Spray

Steam boost: 200 g
Vertical steaming
Ionic deep steam
Variable steam settings

