

PHILIPS

Steam iron


Azur Performer Plus

Steam 50g/min; 210g steam boost

T-ionicGlide soleplate

Safety Auto off + Anti-calc

2600 Watts



GC4526/20



Faster*, Easier and Smarter

More effective calc clean with calc container

The Philips steam iron Azur Performer Plus combines powerful performance with ease of use. The Built-In calc container for effective calc removal for long lasting steam performance, Auto steam control and T-ionicGlide soleplate .

Fast and powerful performance

- 2600 W for quick heat up and powerful performance
- Steam output of up to 50 g/min for better crease removal
- Steam boost up to 210g

Easy gliding on all fabrics

- T-ionicGlide: our best 5-star rated soleplate

Calc solution

- Built-In calc container collects calc during ironing
- Self-Clean for effective calc removal

Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Triple precision tip for optimal control and visibility
- Optimal weight for easier manoeuvrability over your garments
- Electronic shut-off when iron is left unattended



asimpleswitch.com

Highlights

2600 W for quick heat up



2600 W for quick heat up and powerful performance.

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Built-In calc container



Our specially designed and built-in calc container collects calc particles during ironing. The Self Clean process flushes the calc out of the iron to maintain consistent ironing performance day after day.

Self-Clean




In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

Auto Steam Control




Auto Steam Control takes away your worry for selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. The Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

Optimal weight



The iron has the optimal weight to move easily over any garment, making ironing less of a hassle and easy to constantly place the iron on the board and back to its heel rest.

Auto shut-off



The electronic shut-off automatically switches the iron off when it is left unattended or tips over.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Easy to use

Water tank capacity: 300 ml

Power cord length: 2 m

Safety auto off

Soft grip

Drip stop

Soleplate name: T-ionicGlide

Comfortable ironing

Cord length: 2 m

Scale management

Descaling and cleaning: Built-in calc container, Self clean

Size and weight

Packaging dimensions (WxHxL):

13.7x16.7x33.2 cm

Product dimensions (WxHxL):

12.88x15.33x31.95 cm

Total weight with packaging: 1,791 kg

Weight of iron: 1,552 kg

Weight of iron + base: 1,569 kg

Fast crease removal

Continuous steam: 50 g/min

Power: 2600 W

Steam boost: 210 g

