

# PHILIPS

## Steam iron

### Azur Performer Plus

Steam 50g/min; 220g steam boost

T-ionicGlide soleplate

Safety Auto off + Anti-calc

2600 Watts



GC4527/00



## Faster\*, Easier and Smarter

More effective calc clean with calc container

The Philips steam iron Azur Performer Plus combines powerful performance with ease of use. The Built-In calc container for effective calc removal for long lasting steam performance, Auto steam control and T-ionicGlide soleplate .

#### Fast and powerful performance

- 2600W for fast iron heat up
- Steam output of up to 50 g/min for better crease removal
- Steam boost up to 220 g to remove toughest creases

#### Easy gliding on all fabrics

- T-ionicGlide: our best 5-star rated soleplate

#### Calc solution

- Built-In calc container collects calc during ironing
- Self-Clean for effective calc removal

#### Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Optimal weight for easier manoeuvrability over your garments
- Triple precision tip for optimal control and visibility



asimpleswitch.com

# Highlights

## Steam up to 50 g/min




Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

## Auto Steam Control



Auto Steam Control takes away your worry for selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

## Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. The Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

## Optimal weight



The iron has the optimal weight to move easily over any garment, making ironing less of a hassle and easy to constantly place the iron on the board and back to its heel rest.

## Built-In calc container



Our specially designed and built-in calc container collects calc particles during ironing. The Self Clean process flushes the calc out of the iron to maintain consistent ironing performance day after day.

## Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

## Steam boost up to 220 g



Steam boost up to 220 g to remove toughest creases

## T-ionicGlide soleplate



T-ionicGlide is our best gliding and scratch-resistant, 5-star rated soleplate with integrated Titanium-Oxide layer.



[asimpleswitch.com](https://www.asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Easy to use

Water tank capacity: 300 ml  
Power cord length: 2 m  
Safety auto off  
Soft grip

## Fast & powerful crease removal

Continuous steam output: 50 g/min  
Power: 2600 W  
Soleplate: T-ionicGlide  
Steam boost: 220 g

## Scale management

Descaling and cleaning: Built-in calc container, Self clean

## Size and weight

Packaging dimensions (WxHxL):  
34,1\*30\*36 cm  
Product dimensions (WxHxL): 16\*32,6\*14 cm  
Total weight with packaging: 1,52 kg  
Weight of iron + base: 1,75 kg

