

# PHILIPS

## Steam iron

### Azur Performer Plus

Steam 50g/min; 220g steam boost

SteamGlide Plus soleplate

Anti-calc

2600 Watts



GC4527/80



## Faster\*, Easier and Smarter

More effective calc clean with calc container

The Azur Performer Plus steam iron combines powerful performance with ease of use. The built-in calc container provides effective calc removal for long-lasting steam performance, auto steam control and SteamGlide Plus soleplate.

#### Fast and powerful performance

- 2600 W for fast iron heat-up
- Steam boost up to 220 g to remove the toughest creases
- Steam output of up to 50 g/min for better crease removal

#### Easy gliding on all fabrics

- SteamGlide Plus soleplate: Our best gliding, faster ironing

#### Calc solution

- Built-In calc container collects calc during ironing
- Self-Clean for effective calc removal

#### Comfortable ironing

- Auto Steam Control for the right steam for each garment
- Optimal weight for easier manoeuvrability over your garments
- Triple precision tip for optimal control and visibility
- Electronic shut-off when iron is left unattended



# Highlights

## 2600 W for fast heat-up



The 2600 W Azur Performer Plus steam iron will heat up very quickly, and deliver powerful performance for superb ironing results.

## Auto Steam Control



Auto Steam Control takes away the worry of selecting the amount of steam you need. Just select the temperature for the garments you're ironing and off you go.

## Auto shut-off



The electronic shut-off automatically switches the iron off when it is left unattended or tips over.

## Built-In calc container



Our specially designed and built-in calc container collects calc particles during ironing. The Self Clean process flushes the calc out of the iron to maintain consistent ironing performance day after day.

## Optimal weight



The iron has an optimal weight for moving easily over any garment, making ironing less of a hassle and making it easy to move the iron constantly between the board and its heel rest.

## Self-Clean



In addition to the built-in calc container, the self-clean function of your soleplate will remove the most stubborn calc. A clean soleplate will improve your steam performance and ironing results.

## Steam boost up to 220 g




Steam boost up to 220 g to remove the toughest creases

## SteamGlide Plus soleplate



Our best-gliding SteamGlide Plus soleplate to whizz through your ironing. The carefully designed vents ensure a well-balanced steam distribution.

## Triple Precision Tip



The pointed tip on the Philips Azur Performer is very precise in 3 ways: it has a pointed tip, a button groove and a sleek nose design. The Triple Precision tip enables you to reach into even the trickiest areas, e.g. around buttons or between pleats.

# Specifications

## Easy to use

Water tank capacity: 300 ml  
Power cord length: 3 m  
Soft grip

## Fast and powerful crease removal

Continuous steam output: 50 g/min  
Power: 2600 W  
Steam boost: 220 g

## Scale management

Descaling and cleaning: Built-in calc container, Self-clean

## Size and weight

Packaging dimensions (W x H x D): 34,1 x 30 x 36 cm  
Product dimensions (W x H x D): 16 x 32,6 x 14 cm  
Total weight with packaging: 1.75 kg  
Weight of iron: 1.52 kg

