

PHILIPS

Steam iron

Azur Ionic

Ionic Deepsteam

GC4630



Removes creases easily from cotton and linen

Powerful ironing with Ionic DeepSteam

Remove even the toughest creases, thanks to Ionic DeepSteam. This powerful steam iron creates 50% smaller steam particles that reach deep into stubborn fabrics like cotton and linen, so you get great results easily!

Easy crease removal from cotton and linen

- 50% smaller steam particles reach deeper into tough creases
- Steam boost up to 150 g for the most stubborn creases
- SteamGlide soleplate is Philips premium soleplate
- Continuous steam output up to 40 g/min

Safe ironing

- Electronic safety shut-off when iron is left unattended

Comfortable ironing


- Soft grip for lasting ironing comfort

Reaches into tricky areas

- Steam tip allows you to have steam in hard-to-reach areas

Highlights

Ionic DeepSteam




The ionization process creates smaller steam particles that reach deeper into the fabric. This means even the toughest creases are removed easily.

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate. It has great scratch resistancy, glides excellent and is easy to clean.

Automatic safety shut-off



The electronic safety shut-off automatically switches the iron off when it is left unattended or tips over.

Specifications

Accessories

Included in pack: Cord binder for easy cord storage

Comfortable ironing

Additional comfort: 360 degree cord freedom, Soft grip

Anti-scale management: Double Active Calc System

Cord length: 3 m

No leakage: Drip-stop system

Safe in use: Automatic shut-off when iron is left unattended, Exceeds international drop test

standards

Suitable for tap water

Water tank capacity: 335 ml

Crease removal

Continuous steam: Up to 40 gr/min

Ionic Deepsteam: Ionic DeepSteam

reaching tricky areas: Steam tip

Spray

Steam Boost: Up to 150 gr/min

Vertical Steam

Easy to use

Control: Temperature ready light, Variable steam settings

Fast heat-up

Smooth gliding

Soleplate: SteamGlide soleplate

Technical specifications

Frequency: 50-60

Power: 2400

Voltage: 220 - 240

