

PHILIPS

Steam iron

Azur

Auto Shut Off

GC4720



Removes creases easily

Powerful ironing with SteamGlide soleplate

Ironing is smooth and effortless with this iron's SteamGlide soleplate. Its powerful steam and easy gliding make it the ideal combination to remove creases and get great results!

Easily removes creases

- Continuous steam output up to 40 g/min
- Steam boost up to 165 g for the most stubborn creases

Powerful performance

- 2400 Watt enables constant high steam output

Easy gliding on all fabrics

- The perfect balance between gliding and stretching

Comfortable ironing

- Extra long 3 m cord for maximum reach

Reaches into tricky areas

- Steam tip allows you to have steam in hard-to-reach areas

Highlights

SteamGlide PLUS



For the best results you need a soleplate that has the optimal balance between gliding and stretching. This is offered through SteamGlide PLUS with its easy glide zone and perfect stretch zone.

2400 Watt




2400 Watt enables constant high steam output.

Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Extra long 3 m cord



With the extra-long 3-m cord of your Philips iron, you can easily reach right up to the edges of your ironing board - and further!

Automatic safety shut-off



The electronic safety shut-off automatically switches the iron off when it is left unattended or tips over.

Steam boost up to 165 g

The steam boost can be used for vertical steaming and tough creases.

Specifications

Accessories

Included in pack: Cord binder for easy cord storage

Comfortable ironing

Additional comfort: 360 degree cord freedom, Soft grip

Anti-scale management: Double Active Calc System

Cord length: 3 m

No leakage: Drip-stop system

Safe in use: Automatic shut-off when iron is left unattended, Exceeds international drop test standards

Suitable for tap water

Water tank capacity: 350 ml

Crease removal

Continuous steam: Up to 40 gr/min

Reaching tricky areas: Steam tip Spray

Steam Boost: Up to 165 gr/min

Vertical Steam

Easy to use

Control: Temperature ready light, Variable steam settings

Fast heat-up

Smooth gliding

Soleplate: SteamGlide soleplate

Technical specifications

Frequency: 50–60

Power: 2400

Voltage: 220 - 240

Weight: 1.7 kg

Water tank capacity: 350 ml

