

PHILIPS

Steam iron

Azur

Steam 50g/min; 200g steam boost

SteamGlide soleplate

Safety Auto off + Anti-calc

2600 Watts

GC4860/25



Designed for perfection

with heat-resistant storage box

The optimal design and weight of this Azur iron allows you to glide easily on all garments and reach the trickiest areas. Together with its powerful steam performance, it gives you all you need for perfect results. Now with a storage box!

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate
- SteamGlide Plus: perfect mix of gliding and stretching

Longer lifetime

- Double Active Calc System prevents scale build-up

Easily removes creases

- Steam output of up to 50 g/min for better crease removal
- Steam boost up to 200 g
- 2600 W for quick heat-up and powerful performance

Designed for perfect results

- Steam tip allows you to have steam in hard-to-reach areas
- 3 Safety Auto Off triggers

Easy storage

- Heat-resistant storage box for easy storage



asimpleswitch.com

Highlights

SteamGlide soleplate



The SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistance, glides excellently and is easy to clean.

Double Active Calc System



Double active calc

The Double Active Calc system of your Philips steam iron prevents scale build-up through anti-scale pills and an easy-to-use calc clean function.

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

2600 W for quick heat-up

2600 W max


2600 W for quick heat-up and powerful performance.

Steam tip



The unique steam tip of this Philips iron combines a particularly pointed front of the soleplate with special elongated steam slots in the tip to reach right into the smallest and most difficult areas for the best ironing results.

Heat-resistant storage box



This heat-resistant storage box is designed for storing the hot iron easily. For optimal performance and longer lifetime of your box,

always unplug the iron and empty the water tank before storing the iron in the box. When you put a hot iron in the box, the bottom of the box also becomes warm on the outside, but there is no risk of burning.

Safety Auto Off

Safety auto off

Iron shuts off automatically when the iron is held still for 30s on its soleplate, lying on its side for 30s or standing on its heel rest for 8 minutes.

SteamGlide Plus soleplate

For the best results you need a soleplate that has the optimal balance between gliding and stretching. This is offered through SteamGlide Plus with its easy glide zone and perfect stretch zone.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide Plus
Steam boost: 200 g
Vertical steaming
Ionic deep steam
Spray
Steam tip
Variable steam settings

Easy to use

Water tank capacity: 350 ml
Drip stop
Safety auto off
Cord storage: Cord clip
Fast and easy filling
Filling and emptying water: Side-opening

door
Power cord length: 2.5 m
Soft grip

Calc management

Calc clean solution: Double active calc clean

Accessories

Heat-resistant storage box

