

PHILIPS

Steam iron

Azur

Steam 50g/min; 200g steam boost

SteamGlide Plus soleplate

Safety Auto off + Anti-calc

2600 Watts

GC4860/26



Designed for perfection

Optimal design and weight of this Azur iron allows you to glide easily on all garments and reach into the trickiest areas. Together with its powerful steam performance, it gives you all you need for perfect results.

Easy gliding on all fabrics

- SteamGlide Plus: perfect mix between gliding and stretching

Longer lifetime

- Double Active Calc System prevents scale build-up

Easily removes creases

- Steam output of up to 50 g/min for better crease removal
- 2600 W for quick heat up and powerful performance
- Steam boost up to 200 g

Designed for perfect results

- Steam tip allows you to have steam in hard-to-reach areas
- 3 ways of automatic shut-off

Easy storage

- Heat-resistant storage box for easy storage



asimpleswitch.com

Highlights

Double Active Calc System



Double Active Calc system of your Philips steam iron prevents scale build-up through anti scale pills and an easy to use calc clean function.

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

Heat-resistant storage box



This heat-resistant storage box is designed for storing the hot iron easily. For optimal performance and longer lifetime of your box, always unplug the iron and empty the watertank before storing the iron in the box. When you put a hot iron in the box, the bottom of the box also becomes warm on the outside, but there is no risk of burning.

2600 W for quick heat up



2600 W for quick heat up and powerful performance.

Steam tip

The unique steam tip of this Philips iron, combines a particularly pointed front of the soleplate with special elongated steam slots in the tip, to reach right into the smallest and most difficult areas for the best ironing results.

Automatic shut-off



Iron shuts off automatically when the iron is hold still for 30s on soleplate, 30s lying on a side or standing on its heel rest for 8 minutes.

SteamGlide Plus soleplate

For the best results you need a soleplate that has the optimal balance between gliding and stretching. This is offered through SteamGlide Plus with its easy glide zone and perfect stretch zone.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast & powerful crease removal

Continuous steam output: 50 g/min

Power: 2600 W

Soleplate: SteamGlide Plus

Steam boost: 200 g

Vertical steaming

Easy to use

Drip stop

Safety auto off

Water tank capacity: 350 ml

Calc management

Calc clean solution: Double active calc clean

