

# PHILIPS

## Steam iron

### Azur

Steam 50g/min; 200g steam boost

SteamGlide Plus soleplate

Safety Auto Off

2600 Watts

GC4870/02



## Designed for perfection

### Iron with Ionic Deepsteam

This new Philips Azur steam iron comes with the unique Ionic Deepsteam function giving you the best results on tough creases like cotton and linen. Together with its optimised weight and design this iron is designed for perfect results.

#### Easy gliding on all fabrics

- SteamGlide Plus: perfect mix of gliding and stretching

#### Designed for perfect results

- Optimal design to manoeuvre the iron easily over the garment
- Lightweight to move the iron easily on and off the board
- Steam tip allows you to have steam in hard-to-reach areas
- Automatically turned off for safety and energy saving
- Sideways-opening filling door

#### Easily removes creases

- 200 g steam boost
- 2600 W for quick heat-up and powerful performance
- Steam output of up to 50 g/min for better crease removal

#### Ionic DeepSteam


- Smaller steam particles reach deeper into toughest creases



[asimpleswitch.com](http://asimpleswitch.com)


# Highlights

## Steam tip




The unique steam tip of this Philips iron combines a particularly pointed front of the soleplate with special elongated steam slots in the tip to reach right into the smallest and most difficult areas for the best ironing results.

## Easy to handle



The Philips steam iron is designed to move over the garment easily, enabling you to reach even the hardest-to-reach areas easily.

## Lightweight iron



The iron has an optimal weight of 1.6 kg making it easy to constantly place the iron on the board and back to its heelrest.

## 200 g steam boost



200 g steam boost

## 2600 W for quick heat-up




2600 W for quick heat-up and powerful performance.

## Steam up to 50 g/min




Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

## Ionic DeepSteam




The ionisation process creates smaller steam particles that reach deeper into the fabric. This means even the toughest creases are removed easily.

## Safety auto off



The safety auto-off function automatically switches off the appliance if it has not been used for 5 minutes, to save energy.

## Easy filling



## Sideways opening

Sideways-opening filling door

## SteamGlide Plus soleplate

For the best results you need a soleplate that has the optimal balance between gliding and stretching. This is offered through SteamGlide Plus with its easy glide zone and perfect stretch zone.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Fast and powerful crease removal

Soleplate: SteamGlide Plus  
Continuous steam output: 50 g/min  
Steam boost: 200 g  
Vertical steaming  
Ionic deep steam  
Variable steam settings  
Spray  
Steam tip  
Power: 2600 W

## Easy to use

Water tank capacity: 350 ml  
Drip stop  
Soft grip  
Safety auto off  
Cord storage: Cord clip  
Power cord length: 2.5 m  
Filling and emptying water: Side-opening door

## Calc management

Calc clean solution: Double active calc clean

## Technical specifications

Weight of iron: 1.6 kg  
Voltage: 220 - 240 V

