

PHILIPS

Steam iron

Azur

Steam 45g/min; 200g steam boost

SteamGlide soleplate

Safety Auto Off

2400 Watts

GC4875/22



Designed for perfection

Steam Iron with Ionic Deepsteam

This new Philips Azur iron comes with the unique Ionic Deepsteam function giving you the best results on tough creases like cotton and linen. Together with its optimized weight and design this iron is simply designed for perfect results.

Easy gliding on all fabrics

- SteamGlide soleplate is Philips premium soleplate

Designed for perfect results

- Optimal design to manoeuvre the iron easily over the garment
- Lightweight to move the iron easily on and off the board
- Steam tip allows you to have steam in hard-to-reach areas
- Automatically turned off for safety and energy saving
- Sideways opening filling door

Easily removes creases

- 2400 W for quick heat up
- Steam output of up to 45 g/min for better crease removal
- 170 g steam boost for the most stubborn creases

Ionic DeepSteam

- Smaller steam particles reach deeper into toughest creases

Highlights

Steam tip



Steam tip


The unique steam tip of this Philips iron, combines a particularly pointed front of the soleplate with special elongated steam slots in the tip, to reach right into the smallest and most difficult areas for the best ironing results.

SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.


Easy to handle



Easy to handle

The Philips steam iron is designed to manoeuvre it easily over the garment and enabling you to reach easily even the hardest to reach areas.

Lightweight iron



The iron has an optimal weight of 1.6kg making it easy to constantly place the iron on the board and back to its heelrest.

2400 W for quick heat up

2400W
max

2400 W for quick heat up and powerful performance


Steam up to 45 g/min



45 g


Continuous steam output of up to 45 g/min gives you the perfect amount of steam to efficiently remove all creases.

Ionic DeepSteam



The ionization process creates smaller steam particles that reach deeper into the fabric. This means even the toughest creases are removed easily.

Easy filling



Sideways opening

Sideways opening filling door

Automatic shut-off

Safety
auto
off

The safety auto off function automatically switches off the appliance if it has not been used for a few minutes, also saving energy.

170 g steam boost



Applying the steam boost will release a steam shot up to 170 g to remove even the toughest creases

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide
Continuous steam output: 45 g/min
Steam boost: 170 g
Vertical steaming
Ionic deep steam
Variable steam settings
Spray
Steam tip
Power: 2400 W

Comfortable ironing

Cord length: 2.5 m

Easy to use
Water tank capacity: 335 ml
Drip stop
Soft grip
Safety auto off

Cord storage: Cord clip
Power cord length: 2.5 m
Fast and easy filling

Calc management

Calc clean solution: Double active calc clean

Technical specifications

Weight of iron: 1.6 kg
Voltage: 220 - 240 V

