

PHILIPS

Steam iron

Azur Pro

3000 Watts

50 g/min; 220 g steam boost

T-ionicGlide Soleplate

Safety auto off + anti-calc



GC4885/00



Powerful perfection, every time

Iron away creases fast with powerful steam

Azur Pro steam iron enables you with a powerful steam to cut through your ironing in no time and achieve perfect results. Maintain control, ultra-fast gliding, easy calc-clean and a larger water tank make your ironing sessions much easier.

Fast and powerful performance

- 3000 W for quick heat-up and powerful performance
- Steam output of up to 50 g/min for best crease removal
- Steam boost up to 220 g to remove toughest creases

Comfortable ironing

- Less refilling with very large 350ml water tank
- Easy grip for convenient handling while ironing
- Large 2,5 m cord for great reach on the ironing board
- Pointed tip for optimal control and visibility

Safe ironing

- Quick calc release to remove scale from your steamer
- Iron switches off automatically when left unattended

Easy gliding on all fabrics

- T-ionicGlide: our best 5-star rated soleplate

Highlights

3000 W for fast heat up



Delivers a fast warm-up and powerful performance to get your ironing done quickly

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Steam boost up to 220 g



Steam boost up to 220 g to remove toughest creases

Easy grip



A well designed, soft grip on the top of the steam iron will make your ironing session more comfortable.

T-ionicGlide soleplate




T-ionicGlide is our best gliding and scratch-resistant, 5-star rated soleplate with integrated Titanium-Oxide layer.

350 ml water tank



Less refilling with the very large 350 ml water tank so you can iron more clothes in one go.

Pointed tip




Pointed tip for optimal control and visibility

Automatic shut-off



The steam iron shuts off automatically when left unattended. It will switch off after 8 minutes when left standing on its heelrest and after 30 seconds when left resting on its soleplate or sides.

2,5 m cord



A large 2,5 m cord gives you the reach you need during your ironing. Now you reach every corner of your ironing board without any problems.

Quick calc release



Quick calc release is the easiest way to remove scale from your iron and guarantees consistently powerful steam for years to come.

Specifications

Easy to use

Power cord length: 2.5 m
Safety auto off
Soft grip
Water tank capacity: 350 ml
Drip Stop
Tap water suitable

Fast crease removal

Continuous steam: 50 g/min
Power: 3000 W
Steam boost: 220 g

Vertical steam

Voltage: 220-240 V
Water spray

Green efficiency

Energy saving mode
Energy saving*: 20 %
User manual: 100% recycled paper

Guarantee

2 year worldwide guarantee

Scale management

Descaling and cleaning: Double active calc clean, Self clean

Size and weight

Weight of iron: 1.5 kg

