

PHILIPS

Steam iron

Azur Pro

3000 Watts

50 g/min; 230 g steam boost

T-ionicGlide Soleplate

Safety auto off + anti-calc



GC4887/30



Powerful perfection, every time

Iron away creases fast with powerful steam

Azur Pro steam iron enables you with powerful steam to cut through your ironing in no time and achieve perfect results. Ironing is now easy with ultra-fast gliding, a larger water tank and built-in calc container

Fast and powerful performance

- 3000 W for quick heat-up and powerful performance
- Steam output of up to 50 g/min for best crease removal
- Steam boost up to 230g

Easy gliding on all fabrics

- T-ionicGlide: our best 5-star rated soleplate

Comfortable ironing

- Less refilling with very large 350ml water tank
- Easy grip for convenient handling while ironing
- Large 2,5 m cord for great reach on the ironing board
- Pointed tip for optimal control and visibility

Safe ironing

- Built-In calc container collects calc during ironing
- Iron switches off automatically when left unattended

Highlights

3000 W for fast heat up



Delivers a fast warm-up and powerful performance to get your ironing done quickly

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Easy grip



A well designed, soft grip on the top of the steam iron will make your ironing session more comfortable.

T-ionicGlide soleplate




T-ionicGlide is our best gliding and scratch-resistant, 5-star rated soleplate with integrated Titanium-Oxide layer.

350 ml water tank



Less refilling with the very large 350 ml water tank so you can iron more clothes in one go.

Pointed tip



Pointed tip for optimal control and visibility

Built-in calc container



Our specially designed and built-in calc container collects calc particles during ironing. The Self Clean process flushes the calc out of the iron to maintain consistent ironing performance day after day.

Automatic shut-off



The steam iron shuts off automatically when left unattended. It will switch off after 8 minutes when left standing on its heelrest and after 30 seconds when left resting on its soleplate or sides.

2,5 m cord



A large 2,5 m cord gives you the reach you need during your ironing. Now you reach every corner of your ironing board without any problems.

Steam boost up to 230g



Steam boost up to 230g for fast removal of even the most stubborn creases.

Specifications

Fast crease removal

Continuous steam: 50 g/min
Power: 3000 W
Steam boost: 230 g
Vertical steam
Voltage: 220-240 V
Water spray

Easy to use

Water tank capacity: 350 ml
Drip Stop
Power cord length: 2.5 m

Safety auto off
Soft grip
Tap water suitable

Fast & powerful crease removal

Soleplate: T-ionicGlide

Scale management

Descaling and cleaning: Double active calc clean, Built-in calc container, Self clean

Size and weight

Packaging dimensions (WxHxL):
34,1*30*36 cm
Product dimensions (WxHxL): 16*32*14 cm
Total weight with packaging: 1,75 kg
Weight of iron: 1.5 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
Energy saving*: 20 %
User manual: 100% recycled paper

