

PHILIPS

Steam iron

Azur

Steam 50g/min; 200g steam boost

Anodilium soleplate

Safety Auto Off

2600 Watts

GC4891/02



2600W Power tool for ironing

Powerful iron with more steam

This powerful Philips iron comes with the most robust soleplate of all irons. Nothing can scratch this iron while it glides smoothly over your garment. The powerful steam boost helps you to blast all creases away easily.

Easy gliding on all fabrics

- Scratch-resistant, highly durable Anodilium soleplate

Reaches into tricky areas

- Steam tip allows you to have steam in hard-to-reach areas

Safe ironing

- Drip-stop system keeps your garments spotless while ironing
- Automatically turned off for safety and energy saving

Easy crease removal from cotton and linen

- Steam output of up to 50 g/min for better crease removal
- 200 g steam boost

Highlights


Anodilium soleplate



Anodilium

Excellent gliding, excellent scratch resistance, excellent to clean, excellent durability!

Steam tip



Steam tip

The unique steam tip of this Philips iron, combines a particularly pointed front of the soleplate with special elongated steam slots in the tip, to reach right into the smallest and most difficult areas for the best ironing results.

Drip-stop system



Drip stop

The Drip Stop system of your Philips steam iron lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Steam up to 50 g/min



50 g

Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Automatic shut-off

Safety auto off

The safety auto off function automatically switches off the appliance if it has not been used for a few minutes, also saving energy.

200 g steam boost



200 g steam boost

Specifications

Fast & powerful crease removal

Soleplate: Anodilium
 Continuous steam output: 50 g/min
 Steam boost: 200 g
 Vertical steaming
 Variable steam settings
 Spray
 Power: 2600 W

Comfortable ironing

Cord length: 2.5 m

Easy to use

Water tank capacity: 350 ml
 Drip stop
 Safety auto off
 Cord storage: Cord clip
 Power cord length: 2.5 m
 Fast and easy filling

Calc management

Calc clean solution: Double active calc clean

Technical specifications

Weight of iron: 1.6 kg
 Voltage: 220 - 240 V

Accessories

Heat-resistant storage box

