

Philips Azur
Steam iron

50g/min continuous steam
220g steam boost
SteamGlide Elite soleplate

GC4902



Perfect results, every time

With our best scratch resistant soleplate

Long lasting performance with Quick Calc Release and SteamGlide Elite soleplate with enhanced scratch resistance.

Faster ironing and powerful performance

- Up to 220g steam boost blasts stubborn creases
- 2800W for quick heat-up and powerful performance
- Steam output of up to 50 g/min for best crease removal

Comfortable ironing

- Quick calc release system for an easy cleaning of your iron
- Automatic shut-off when the iron is left unattended

Easy gliding on all fabrics

- SteamGlide Elite: Our best gliding and scratch resistance

PHILIPS

Steam iron
50g/min continuous steam 220g steam boost, SteamGlide Elite soleplate

Specifications

Technology

- For all ironable fabrics

Fast crease removal

- Continuous steam: 50 g/min
- Power: 2800 W
- Pressure: 50g/min
- Ready to use: 2 min
- Steam boost: 220 g
- Variable steam levels
- Vertical steam
- Voltage: 240 V
- Water spray

Easy to use

- Soleplate gliding performance: 4 stars
- Soleplate name: SteamGlide Elite
- Water tank capacity: 300 ml
- Cord freedom (swivel): 360 degree cord freedom
- Drip Stop
- Integrated power plug
- Power cord length: 2.5 m
- Select steam level from handle

- Soleplate scratch resistance: 5 stars
- Tap water suitable
- Auto shut-off
- Indicator light

Scale management

- Descaling and cleaning: Quick Calc Release

Size and weight

- Packaging dimensions (WxHxL): 13.7 x 16.7 x 33.2 cm
- Product dimensions (WxHxL): 12.88 x 15.33 x 31.95 cm
- Total weight with packaging: 1.908 kg
- Weight of iron: 1.669 kg

Guarantee

- 2 year worldwide guarantee

Green efficiency

- Product packaging: 100% recycable
- User manual: 100% recycled paper

GC4902/26R1

Highlights

Steam boost up to 220g



Penetrates deeper into fabrics to easily remove stubborn creases.

2800W to heat-up quickly

Delivers a fast warm-up and powerful performance to get your ironing done quickly.

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Quick Calc Release



Quick Calc Release for an easy cleaning of your iron and a long-lasting steam performance

Auto shut-off

The iron shuts itself off if you leave it standing still. On its soleplate, it will automatically switch off after 30 seconds. On its heel rest, it will automatically switch off after 8 minutes.

SteamGlide Elite soleplate

Our exclusive SteamGlide Elite is our best soleplate for ultimate gliding and maximum scratch resistance.



Issue date 2020-08-11

Version: 2.1.1

12 NC: 0000 041 04648
EAN: 87 10895 69816 0

© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com